
Non-Metallic Surface Raceway



QUICK REFERENCE GUIDE

Pan-Way[®] LD Series



Example part: LD3IW6-A
Colors: IW, EI, WH


- One-piece single-channel latching design
- Pre-applied adhesive backed tape

- For routing data and low voltage cabling only (50 V or less)
- Available lengths – 6', 8', 10'



0.77" × 0.46"
A=0.21 in.²

LD3 Series



1.01" × 0.58"
A=0.38 in.²

LD5 Series



1.51" × 0.94"
A=1.00 in.²

LD10 Series


Pan-Way[®] LDPH Series



Example part: LDPH3IW8-A
Colors: IW, EI, WH


- Two-piece single-channel latching design
- Pre-applied adhesive backed tape with screw mountable option

- For routing cables up to 600 V
- Available lengths – 6', 8', 10'




0.75" × 0.41"
A=0.17 in.²

LDPH3 Series



1.02" × 0.55"
A=0.33 in.²

LDPH5 Series



1.52" × 0.86"
A=0.89 in.²

LDPH10 Series


Pan-Way[®] T-45 Series



Example part: T45BIW8-A
Colors: IW, EI, WH

- Two-piece single-channel with snap-in divider design

- Multi-directional cover hinge allows cable installation from either side
- Available with/without adhesive backed tape
- Available lengths – 8', 10'



2.38" × 1.25"
A=2.12 in.²

T-45 Series

IW **EI** **WH**

Note: Colors shown may differ slightly from actual raceway colors.
IW=Off White, EI=Electric Ivory, WH=White.


Pan-Way[®] T-70 Series



Example part: T70BIW8
Colors: IW, EI, WH

- Two-piece single-channel with snap-in divider design

- Transitions to T-45 and LD profile raceways
- Available lengths – 6', 8', 10'



4.07" × 1.77"
A=5.15 in.²

T-70 Series

Non-Metallic Surface Raceway

Quick Reference Guide


Pan-Way® Above Floor Raceway Series



Example part: AFR4BCBL6
Colors: Black (BL),
Office Slate (OS)

- Four channel raceway with snap on cover design

- Channel keep data and power separate
- Non-Metallic
- Available lengths — 6'



0.50" Height
6.93" Width

AFR48BC6 Series

Accessories



Pan-Way® Faceplates



Low Voltage Fittings



One-inch Bend Radius Fittings



Pan-Way® Junction Boxes

¹ Office raceway also available in addition to raceway styles listed. For a complete part listing, visit www.panduit.com for our on-line catalog.

² Color availability varies among styles, and certain colors may be limited to specific lengths.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

PANDUIT®

For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

©2022 Panduit Corp.
ALL RIGHTS RESERVED.
Printed in the U.S.A.
SRS03--WW-ENG
2/2022