

PIN #	COLOR
1	BROWN
2	BLUE
3	N/A
GND	GREEN / YELLOW

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/6/2012	DCT



SCREW AND FLAT GASKET SUPPLIED WITH EACH CABLE  
NOT SHOWN FOR CLARITY




TABLE A		
P/N	L	STD?
VEN-F20-00	.5M	NO
VEN-120-00	1M	NO
VEN-220-00	2M	YES
VEN-320-00	3M	NO
VEN-420-00	4M	NO
VEN-520-00	5M	YES
VEN-620-00	6M	NO
VEN-A20-00	10M	YES

PARTS LISTED AS NOT BEING STANDARD  
MAY REQUIRE MINIMUM ORDERS

MATERIALS	
BODY:	BLACK POLYAMIDE
CONTACTS:	SILVER PLATED COPPER ALLOY
INSERT:	POLYAMIDE
CABLE:	BLACK PVC
GASKET:	THERMOPLASTIC
SCREW:	ZINC PLATED STEEL
WIRE:	4X20AWG; CABLE OD 0.23"
TEMP:	-40°C TO +80°C (-40°F TO +176°F)
PROTECTION:	IP 65

UNLESS OTHERWISE SPECIFIED:		NAME
DIMENSIONS ARE IN INCHES & [MM]	DRAWN	CAM
	CHECKED	
	ENG APPR.	
	MFG APPR.	
	Q.A.	
MATERIAL	COMMENTS:	
FINISH		
DO NOT SCALE DRAWING		

MENCOM CORPORATION		
TITLE: DIN FORM C CABLE		
SIZE <b>B</b>	DWG. NO. VEN-ZZ20-00	REV <b>A</b>
SCALE: 2:1	WEIGHT:	SHEET 1 OF 1

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MENCOM CORPORATION. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MENCOM CORPORATION IS PROHIBITED.