

PIN #	COLOR
1	BROWN
2	BLUE
GND	GREEN / YELLOW






TABLE A		
P/N	L	STD?
VCN-120-00	39" [1M]	NO
VCN-220-00	79" [2M]	YES
VCN-320-00	118" [3M]	NO
VCN-420-00	157" [4M]	NO
VCN-520-00	197" [5M]	YES
VCN-620-00	236" [6M]	NO
VCN-A20-00	393" [10M]	YES

PARTS LISTED AS NOT BEING STANDARD
MAY REQUIRE MINIMUM ORDERS

MATERIALS	
BODY:	BLACK POLYAMIDE
CONTACTS:	SILVER PLATED COPPER ALLOY
INSERT:	POLYAMIDE
CABLE:	BLACK PVC
GASKET:	THERMOPLASTIC
SCREW:	ZINC PLATED STEEL
TEMP:	-40°C TO +80°C (-40°F TO +176°F)
PROTECTION:	IP 65



250VAC/DC
3 POLES + GND

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
MENCOM CORPORATION. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
MENCOM CORPORATION IS
PROHIBITED.

VOLTS	250V
AMPS	10A
TEMP:	80°C

UNLESS OTHERWISE SPECIFIED:	DRAWN BY	ADM
DIMENSIONS ARE IN INCHES AND [MM]	DRAWN DATE	06/07/2022
	CHECKED BY	
	CHECK DATE	
	COMMENTS:	
MATERIAL		
FINISH		
DO NOT SCALE DRAWING		

MENCOM CORPORATION		
TITLE:		
DIN C W/O ELECT 2+E		
SIZE	DWG. NO.	REV
B	VCN-ZZ20-00	B
SCALE: 2:1	WEIGHT:	SHEET 1 OF 1