



## VWDI08 AC

115V SHADED POLE OPEN FAN COOLED AC DESIGN

Our VWDI08 offers up to 113 in-lbs of torque.

### Specifications

Gearhead		Motor	Additional Information
Gearing:	Plastic high speed and steel	Motor Type: Shaded pole	Current drawings and stock status available at <a href="http://www.bisongear.com">www.bisongear.com</a> <b>ISIS</b> - Products available off-shelf <b>SNS</b> - Min. order quantity and lead time
Housing:	Precision machined die cast zinc	Rotation: CW facing output shaft	
Lubrication:	Grease	Bearings: Ball	
Bearings:	Porous bronze sleeve	Insulation: Class B minimum	
Shafts:	Hardened steel	Enclosure: OFC	
Mounting:	All positions	<b>Features</b>	
Finish:	Unpainted	Units comply with applicable UL & CSA standards	

### VWDI08 Shaded Pole 115V

Model #	Speed (RPM)	Torque (in-lbs)	Input HP	Gear Ratio	Stages	OHL	Amps	Hz	Shipping Wt.
013Q227-0027	60	59	1/10	27	2	150	2.6	60	12.5
013Q227-0052	30	113**	1/10	52	3	150	2.6	60	12.5
013Q227-0128	13	113**	1/10	128	3	150	2.6	60	12.5
013Q227-0250	7	113**	1/10	250	4	150	2.6	60	12.5
<b>With Brake</b>									
013Q207-0027	60	59	1/10	27	2	150	2.6	60	12.5
013Q207-0052	30	113**	1/10	52	3	150	2.6	60	12.5
013Q207-0128	13	113**	1/10	128	3	150	2.6	60	12.5
013Q207-0250	7	113**	1/10	250	4	150	2.6	60	12.5
013Q207-0750	2	113**	1/10	750	5	150	2.6	60	12.5

\*\* Gear Limited (check website for updated information.)

