


USB-to-CAN II Sub-D9 / RJ45 adaptor



Pin Nr. RJ45 Male		Pin Nr. Sub-D9 Male	Signal (If used in conjunction with USB-to-CAN II)
1	-	7	CAN high
2	-	2	CAN low
3	-	3	GND
4	-	4	CAN high (Fault tolerant, only automotive)
5	-	1	CAN low (Fault tolerant, only automotive)
6	-	5	LIN (only automotive)
7	-	6	GND
8	-	9	V-LIN (12V DC, max. 200mA, only automotive)
N.A.	-	8	-
Shield	-	Shield	