

FEATURES

- 50 Ω impedance
- Operating frequency is 4GHz
- Nickel plated body provides high load structure quality
- Gold-plated contacts ensure maximum efficiency

RS PRO Family Name

RS Stock No.: 2469479



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Brass main body TNC connector with PTFE insulation and gold plated contacts.

General Specifications

Type of coaxial connector	TNC connector
Body Orientation	Straight
Body Plating	Nickel 100u"
Body Material	Brass
Termination Method	Crimp
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Mounting Type	Cable Mount
Insulation Material	PTFE

Electrical Specifications

Temperature Range	-65° ~+165°
Characteristic Impedance	50Ω
Frequency Range	0~4GHz
Working Voltage	500V
Insulation Resistance	≥1000MΩ
Medium Pressure	1000V(rms)
VSWR	≤1.3
Working Life	500Cycles

Protection Category

--	--

Additional Information

EAN	
Custom Tariff Number	

Classification

eCI@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
8004334	RS PRO	RF coaxial connector	50Ω impedance	Operating frequency is 4GHz	

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

