

## FEATURES

- Operating frequency is 3GHz
- Nickel plated body
- Gold-plated centre contacts
- Crimp termination method
- ensure maximum efficiency

## RS PRO Family Name

RS Stock No.: 2469460



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The panel mount bulkhead fitting BNC connector has nickel plated body, gold plated centre contact and is suitable for RG58 cables. This 50  $\Omega$  straight BNC connector comes with cable jack, crimp termination.

### General Specifications

Type of coaxial connector	BNC female
Body Orientation	Straight
Polarity	Normal
Mounting Type	Cable Mount
Body Plating	Nickel
Body Material	Copper
Contact Material	Copper
Contact Plating	Gold
Termination Method	Crimp
Gender	Female
Insulation Material	PTFE
Cable	RG58

### Electrical Specifications

Temperature Range	-40° ~ +85°
Impedance	50 $\Omega$
Frequency Range	0~3GHz
Voltage Rating	500 V
VSWR	1.5MAX
Working Life	500Cycles

### Protection Category

--	--

**Additional Information**

EAN	
Custom Tariff Number	

**Classification**

eCl@ss (Version)	
UNSPSC (Version)	

**Approvals**

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

**Similar Products**

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
5463743	RS PRO	RF coaxial connector	Gold plated centre contacts	Operating frequency is 3GHz	

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

