



Quality Products. Service Excellence.

Type 3/12/4 Mild Steel Junction Box C3SC Series

Heavy Duty Screw Cover



Application

- Designed for use as a wiring box, junction box, terminal or pull box in indoor or outdoor applications where subject to windblown dust or rain.

Standards

- UL 508A Listed; Type 3, 4, 12
- cULus Listed per CSA C22.2 No 94; Type 3, 4, 12
- Complies with
 - NEMA Type 3, 4 and 12
 - IEC 60529, IP66

Construction

- 14 gauge steel body up to 24"x24"; 12 gauge body when 30"x30" or larger
- 14 gauge steel cover up to 12"x12"; 10 gauge cover when 16"x16" or larger
- Smooth, continuously welded seams without knockouts, cutouts, or holes
- Captivated stainless steel cover screws thread into sealed wells
- Seamless poured-in place gasket
- No provision for inner mounting panel
- Mounting Foot Kit sold separately - use **C3MTGFOOT**

Finish

- Enclosure and cover are finished with an ANSI 61 gray powder coating inside and outside



Part No.	Enclosure		
	H	W	D
C3SC664GY	6.00	6.00	4.00
C3SC666GY	6.00	6.00	6.00
C3SC864GY	8.00	6.00	4.00
C3SC884GY	8.00	8.00	4.00
C3SC886GY	8.00	8.00	6.00
C3SC888GY	8.00	8.00	8.00
C3SC10104GY	10.00	10.00	4.00
C3SC10106GY	10.00	10.00	6.00
C3SC1084GY	10.00	8.00	4.00
C3SC12106GY	12.00	10.00	6.00
C3SC12124GY	12.00	12.00	4.00
C3SC12126GY	12.00	12.00	6.00
C3SC12128GY	12.00	12.00	8.00
C3SC16126GY	16.00	12.00	6.00
C3SC16166GY	16.00	16.00	6.00
C3SC16168GY	16.00	16.00	8.00
C3SC18186GY	18.00	18.00	6.00
C3SC20208GY	20.00	20.00	8.00
C3SC24208GY	24.00	20.00	8.00
C3SC242410GY	24.00	24.00	10.00

Part No.	Enclosure		
	H	W	D
C3SC242412GY	24.00	24.00	12.00
C3SC24246GY	24.00	24.00	6.00
C3SC24248GY	24.00	24.00	8.00
C3SC303012GY	30.00	30.00	12.00
C3SC363612GY	36.00	36.00	12.00

Tags: **junction box, terminal box, wiring box, pull box, indoor, outdoor, Type 4, Type 12, NEMA 4, NEMA 12, NEMA 3, steel**

Data subject to change without notice

© 2023. Hammond Manufacturing Ltd. All rights reserved.