

Part number

CCFA 1.5



Female crimp contact, CC series, 16 A, turned silver plated, wire cross section 1,5 mm², AWG 16

Product description		Material properties	
Product type	Crimp contact	Main material	Copper alloy
Series	CC		Compliant with exemption
Gender	Female	RoHs conformity	6(c): copper alloy containing up to 4% lead by weight
Technical data		China RoHs - EFUP	50
Current	16 A	REACH SVHC substances	Yes Lead
Wire cross-section	1,50 mm ²	SCIP number	C0979fba-9907-458f-a94a-db781440f273
AWG size	16	Approvals / Standards	
Contact type	Turned silver plated	Certifications	CSA, EAC
Further technical details		UL	ECBT2
Weight	1,50 g	General ordering information	
Conductors stripping length	7,5 mm	EAN13 code	8015747011693
		eCl@ss 8.1	27440204
		ETIM 7.0	EC000796
		Packaging Information	
		Packaging length	112,00 mm
		Packaging height	95,00 mm
		Packaging width	117,00 mm
		Packaging weight	1,47 kg
		Packaging volume	1,24 dm ³
		Packaging description	Carton box
		Packaging quantity	800 Pcs
		Packaging EAN code	8015747103848
		Sub-packaging length	50,00 mm
		Sub-packaging height	44,00 mm
		Sub-packaging width	50,00 mm
		Sub-packaging weight	0,18 kg
		Sub-packaging volume	0,11 dm ³
		Sub-packaging description	Plastic box
		Sub-packaging quantity	100 Pcs
		Sub-packaging EAN barcode	8015747011709

Part number

CCFA 1.5



Catalogue drawings



CCF, CCM and CC..AN contacts

conductor section mm ²	conductor slot $\varnothing A$ (mm)	conductors stripping length (mm)
0,14-0,37	0,9	7,5
0,5	1,1	7,5
0,75	1,3	7,5
1,0	1,45	7,5
1,5	1,8	7,5
2,5	2,2	7,5
3	2,55	7,5
4	2,85	7,5

Notes

Dimensions shown in mm are not binding and may be changed without notice.

California Proposition 65 Information



WARNING

This product can expose you to lead and its compounds, known to the State of California to cause cancer and/or reproductive toxicity. For more information go to www.P65Warnings.ca.gov.
