

Han-INOX® 16B-C-DL-seal



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 016 5402
Specification	Han-INOX® 16B-C-DL-seal

Identification

Category	Accessories
Series of hoods/housings	Han-INOX®
Type of hood/housing	Protection cover
Description of hood/housing	for hoods Metal With fixing cord (loop)

Version

Size	16 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Colour (hood/housing)	Unpainted
Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	215.9 g
Country of origin	Romania
European customs tariff number	85389099
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors