## TRIPP-LITE

### Power It! 2-Outlet In-Desk Power and Charging Dock - 4x USB-A, USB-B, HDMI, RJ11, RJ45, 10 ft. Cord, Antimicrobial Protection, Black

### MODEL NUMBER: PS222DATAM



Installs level with your desktop surface to charge and power multiple devices simultaneously.

#### Features

#### Fits into Your Desktop Surface for Reliable Power and Charging

This Power It!® dock is designed for installation in your workspace's level surface, where its ports are within a convenient arm's reach. When not being used to power or charge devices or connect to a telephone or Ethernet network, you can close the flip-top cover flush against the tabletop to save valuable space. To connect devices, simply pop up the secure cover. This In-Desk Power and Charging Dock is ideal for home and office workstations with limited desk space.

#### A Variety of Ports and Outlets Accept a Wide Range of Electronic Devices

Two NEMA 5-15R outlets and two USB-A ports (4.5A combined) are available for powering and charging your laptop, tablet, smartphone or other devices. The PS222DATAM also features two USB-A data ports for transferring images, documents and other files, as well as ports for connecting HDMI, USB-B, telephone and Ethernet devices. The 10-foot (3-meter) input cord connects to a compatible AC wall outlet.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Environment

The PS222DATAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

### **Specifications**

OVERVIEW		
UPC Code	037332271891	
Device Compatibility	Amazon Kindle; Laptop; Phone; Tablet	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	

#### Highlights

- Installs flush with your tabletop surface to save space and offer easy access
- 2 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 2 USB-A ports share 4.5A for fast charging of phones and other mobile devices
- HDMI, USB-B, RJ11, RJ45 and 2 USB-A data ports connect a wide range of devices
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

#### **Package Includes**

- PS222DATAM 2-Outlet In-Desk Power and Charging Dock
- Owner's manual

# TRIPP-LITE

[		
Recommended Electrical Service	120V	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	10	
Right-Angle Plug	No	
Input Cord Length (m)	3.05	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(2) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	No	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & COM	NTROLS	
Diagnostic LED(s)	Yes	
CHARGING		
Number of Charging Ports	2	
Total Charging Amps	4.5A	
Total Charging Watts	22.5	
Charging Method	USB	
Charging Port Type	(2) USB A (FEMALE)	
Charging Ports / Amps	(1) 2.1A; (1) 2.4A	
Charging Amps per Port	(1) 2.4A; (1) 2.1A	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	Yes	
Telephone/DSL Protection	Yes	
PHYSICAL		
Color	Black	
Material of Construction	Plastic	

# TRIPP-LITE

1000 Eaton Boulevard Cleveland, OH 44122 United States

Power Cord Color	Black	
Mounting Location	Desktop	
Housing Color	Black	
Mounting Holes or Slots	No	
Shipping Dimensions (hwd / in.)	9.06 x 6.30 x 4.72	
Shipping Weight (kg)	1.05	
Unit Dimensions (hwd / in.)	8.760 x 5.930 x 3.670	
Unit Dimensions (hwd / cm)	8.76 x 5.93 x 3.67	
Unit Weight (Ibs.)	2.09	
Unit Weight (kg)	0.95	
Input Cord Color	Black	
Mounting Details	Cut 7.95" (201.93 mm) x 4.06" (103.13 mm) hole for installation	
CONNECTIONS		
Side A - Connector 1	NEMA 5-15P	
Side A - Connector 2	(2) USB B (FEMALE)	
Side A - Connector 3	HDMI (FEMALE)	
Side A - Connector 4	RJ11 (FEMALE)	
Side A - Connector 5	RJ45 (FEMALE)	
Side B - Connector 1	(2) NEMA 5-15R	
Side B - Connector 2	(4) USB A (FEMALE)	
Side B - Connector 3	HDMI (FEMALE)	
Side B - Connector 4	RJ11 (FEMALE)	
Side B - Connector 5	RJ45 (FEMALE)	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	Yes	
Built-In Circuit Breaker	No	
Network Speed Support	1 Gbps (Gigabit)	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 308 (Canada); ICES (Canada); NOM (Mexico); UL 962A; UL Listed; cUL Listed	
Product Compliance	FCC Part 15 Class B (USA); RoHS	
WARRANTY & SUPPORT		



1000 Eaton Boulevard Cleveland, OH 44122 United States

Product Warranty Period (Worldwide)

Lifetime limited warranty



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.