

## 4 Port PCI Express PCIe Serial Combo Card - 2 x RS232 2 x RS422 / RS485

**Product ID:** PEX4S232485



The PEX4S232485 4 Port PCI Express PCIe Serial Combo Card - 2 x RS232 2 x RS422 / RS485 lets you add two RS232, and two RS422/485 serial ports to your PC through a PCI-Express expansion slot.

This PCI express serial card is a single card solution that is compatible with nearly any serial communication protocol, supporting RS-232, RS-422, RS-485 2-wire or RS-485 4-wire operating modes.

A flexible solution for adding serial ports to full-sized, or small form factor systems, the 4-port serial card includes both low and full profile brackets while the included breakout cable helps to avoid cluttered connections.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Monitor and control industrial machines on an assembly line or in a production environment
- POS retail applications in grocery stores, and any other retail store to control keyboards, cash drawers, receipt printers, card readers/card swipes, scales, and elevated displays on poles

- Bank teller workstations in either full profile or low profile versions to control their serial devices such as cash drawers, card readers / card swipes, printers, keypads / pinpads, pen pads
- Self-service automated machines and kiosks to control serial devices such as scales, touchscreens, magnetic card readers, bar code scanners, receipt printers, label printers

## Features

- 4 port (2 x RS232, 2 x RS422/485) serial combo card
- RS232 data transfer rates up to 460 Kbps
- Supports 2-Wire / 4-Wire RS485 modes
- 256-byte deep FIFO per transmitter and receiver
- Standard and low-profile bracket included
- Compliant with PCI-Express Specification 1.0a
- Supports PCI Power Management 1.1

---

## Hardware

Warranty	Lifetime
Ports	4
Interface	Serial
Bus Type	PCI Express
Card Type	Standard Profile (LP bracket incl.)
Port Style	Dongle (Included)
Chipset ID	SystemBase - SB16C1052PCI

---

## Performance

Serial Protocol	RS-232/422/485
Max Baud Rate	460.8 Kbps
Data Bits	5, 6, 7, 8
FIFO	256 Bytes
Flow Control	None, Xon/Xoff, RTS/CTS

Parity	None, Odd, Even, Space, Mark
Stop Bits	1, 1.5, 2
MTBF	85,288 hours
Supported Protocols	RS-232, RS-422, RS-485 2-wire / 4-wire

---

**Connector(s)**

Connector Type(s)	1 - PCI Express x1
External Ports	4 - DB-9 (9 pin, D-Sub)

---

**Software**

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022
------------------	--

---

**Special Notes / Requirements**

System and Cable Requirements	Available PCI Express slot
-------------------------------	----------------------------

---

**Power**

Input Voltage	12V DC
Output Voltage	12V DC

---

**Environmental**

Operating Temperature	0C to 100C (32F to 212F)
Storage Temperature	0C to 150C (32F to 302F)
Humidity	20~80% RH

---

**Physical Characteristics**

Color	Green
Material	Steel
Product Length	5.3 in [13.4 cm]
Product Width	0.6 in [1.4 cm]
Product Height	2.7 in [6.9 cm]

Weight of Product 2.4 oz [67.4 g]

---

**Packaging Information**

Package Quantity 1

Package Length 8.3 in [21.0 cm]

Package Width 5.7 in [14.6 cm]

Package Height 1.6 in [4.1 cm]

Shipping (Package) Weight 13.8 oz [390.0 g]

---

**What's in the Box**

Included in Package

- 1 - PCI Express Serial Combo Card
- 1 - Breakout Cable
- 1 - Low Profile Bracket
- 1 - Driver CD
- 1 - Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***