

6-Port USB Charging Station - 60W USB-C, 2x 20W USB-C, 3x USB-A, PD Charging, Device and Apple Watch Storage

MODEL NUMBER: U280-006-C3A-ST











Safely stores your mobile devices, including Bluetooth headphones and Apple Watch, while charging and organizing up to 6 devices simultaneously.

Features

Flexible USB Charging Station Charges Up to 6 Mobile Devices at the Same Time

At home or in the office, this USB charging station provides enough power and ports to keep your devices at high capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. This compact charging station is ideal for homes with busy families, dorm rooms and offices with multiple mobile devices. It charges up to six devices at the same time, including smartphones, tablets, laptops and e-readers. It doesn't require a computer, so you can take it anywhere AC power is available.

Removable Brackets Allow Convenient and Customizable Storage

Five tall and three short brackets are included to hold multiple devices during charging or to store them and keep them organized when not in use. Also included are special brackets for Bluetooth headphones and an Apple Watch. The brackets easily insert into slots built into the charger's surface. You can customize storage space according to the number and size of the connected devices, ranging from smartphones and AirPods to larger laptops and tablets.

Provides Plenty of Power to Keep Your Devices at Capacity

Three USB-A ports provide a maximum of 5V 2.4A (12W) of power, enough for fast-charging most smartphones and tablets. For devices that are more powerful, one USB-C port provides up to 60W PD charging for battery-intensive devices like the MacBook Pro or Chromebook Pixel. Two more USB-C ports support PD charging up to 20W.

Easy to Use with the Included Power Cord

To charge your USB devices, simply plug the included 120W power supply into any standard NEMA 5-15R outlet, and connect your devices to the available USB ports. The charger protects against overheating, overcurrent and overcharging. A green LED indicates the unit is on and receiving AC power.

Specifications

Highlights

- 3 USB-A ports provide up to 5V 2.4A of charging power each for phones and tablets
- 3 USB-C PD Charging ports provide up to 60W of charging power to compatible devices
- Protects connected devices with built-in safeguards against overheating and overvoltage
- Removable brackets allow convenient customization of storage space for devices
- Operates wherever AC power is available — no computer necessary

Package Includes

- U280-006-C3A-ST 6-Port USB Charging Station
- 120W (20V/6A) external power supply with NEMA 5-15P plug
- (10) Storage brackets
- Quick Start Guide



OVERVIEW	
UPC Code	037332274854
Product Type	Charging Station
Charging Form Factor	Charging Hub
Device Compatibility	Amazon Kindle; Chromebook; Laptop; Phone; Tablet; Watch
Technology	USB
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 3A
AC Power Adapter Output Specs (V / A)	20V / 6A
AC Power Adapter Cord Length (ft.)	3.28
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50 / 60 Hz
OUTPUT	
Overload Protection	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60 Hz, 3A; Output: 20V, 6A
DC Barrel Plug	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	60W
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (x1, Power)
CHARGING	
Number of Charging Ports	6
Total Charging Amps	30
Total Charging Watts	120



Charging Method	USB
Charging Port Type	(3) USB A (FEMALE); (3) USB C (FEMALE)
Charging Ports	(3) 2.4A Quick Charge; USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
Charging Ports Details	(x2) USB-C ports support 20W PD Charging; 5V/3A, 9V/2.22A, 12V/1.66A (20W Max)(x1) USB-C port supports 60W PD Charging; 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3A (60W Max)(x3) USB-A ports support 5V/2.4A (12W)
Charging Ports / Amps	(3) 2.4A; (3) 3A
Overcharge Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	PC (Plastic)
Unit Packaging Type	Вох
ENVIRONMENTAL	
Operating Temperature Range	32° to 131°F (0° to 55°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	0 to 95% RH
CONNECTIONS	
Number of Ports	6
Side B - Connector 1	(3) USB A (FEMALE)
Side B - Connector 2	(3) USB C (FEMALE)
FEATURES & SPECIFICATIONS	
Overvoltage Protection	Yes
Over Current Protection	Yes
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	ICES (Canada); NOM (Mexico)
Product Compliance	FCC (USA); REACH; RoHS; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty







© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.