

10 ft. CAT6 Ethernet cable - 10 Pack - ETL Verified - Blue CAT6 Patch Cord - Snagless RJ45 Connectors - 24 AWG Copper Wire – UTP Ethernet Cable

Product ID: N6PATCH10BL10PK



This blue 10 ft. (3 m) CAT6 Ethernet cable bulk 10 pack meets all Category 6 cable specifications, to deliver a reliable Gigabit network connection.

Protect Your Equipment

These blue CAT6 patch cords are built using 100% copper wire and are tested to comply with ANSI/TIA 568 C.2 Category 6 requirements. We don't use copper-clad aluminum (CCA) wire, which is subject to problems like weak power delivery, heat buildup, equipment damage and possibly fire.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

High-Quality Construction

Each CAT6 Ethernet cable is manufactured using high-quality copper conductors and carefully constructed and tested to keep Near-End Crosstalk (NEXT) well within acceptable limits. The patch cables are constructed with 24 AWG copper wire, to ensure peak performance for demanding Ethernet applications such as Power-over-Ethernet and 4K or 1080p video streaming.

Easily Install Your Network Cables

For trouble-free cable runs, these durable cables feature snagless connectors that protect the RJ45 clips during installation, making them less likely to snag or break.

The CAT6 Ethernet cables also feature molded boots which offer strain relief by stopping the RJ45 connectors from bending at sharp angles. This reduces the risk of cable damage, which could decrease network connectivity and performance.

N6PATCH10BL10PK is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

Features

- **100% COPPER WIRING:** Each CAT6 Ethernet cable is built with 100% copper wiring to prevent weak power delivery and equipment damage, compared to copper-clad aluminum wire cables
- **ETL VERIFIED:** This CAT6 cable 10 pack is ETL Verified to ensure an elevated level of quality and reliability. Each CAT6 patch cord is tested to comply with ANSI/TIA-568-D Category 6 requirements
- **CABLE PERFORMANCE:** Length: 10 ft. (3 m) Color: Blue Cable Structure: 4 Pair UTP Connector Type: Snagless Jacket Material: PVC Wire Gauge: 24 AWG Wiring Standard: ANSI/T568B
- **EASY INSTALLATION:** Blue snagless Ethernet cords won't get caught in wiring conduits during installation; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- **CAT6 PATCH CABLE MULTIPACK:** This 10 pack of 10 ft. Blue patch cords is a convenient and affordable option for businesses in need of multiple snagless ethernet cables

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Snagless
Wiring Standard	TIA/EIA-568-B.1-2001 T568B

Performance

Cable Rating	CAT6 - 650 MHz
--------------	----------------

Connector(s)

Connector A	1 - RJ-45
Connector B	1 - RJ-45

Physical Characteristics

Color	Blue
Wire Gauge	24 AWG
Conductor Type	Stranded Copper
Cable Length	10.0 ft [3.0 m]
Product Length	120.0 in [304.8 cm]
Product Width	0.5 in [1.2 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	4.7 oz [134 g]

Packaging Information

Package Quantity	10
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.3 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	3.0 lb [1.4 kg]

What's in the Box

Included in Package	10 - 10 ft. CAT6 Cables
---------------------	-------------------------

****Product appearance and specifications are subject to change without notice.***