

4U Wall Mount Network Rack- 14 Inch Deep(Low Profile)- 19" Patch Panel Bracket for Shallow Server and IT Equipment, Network Switches- 44lbs/20kg Weight Capacity, Black

**Product ID:** WALLMOUNT4



The 4U 13.78in. (35cm) deep wall-mounting bracket for patch panels and network equipment, delivers a sturdy and dependable equipment storage option, allowing you to wall mount data/IT equipment up to a total of 44lbs. (20kg). It's the perfect solution for areas where space is at a premium like small office/home office environments or spaces with limited server room because it doesn't take up any floor space.

The mounting bracket features an all-steel design and is suitable for mounting patch panels, or other slim 19in rack equipment to a wall, and to organize cabling or equipment in your network closet, wiring closet, back office or IDF. The sturdy steel construction is especially helpful for durability in harsh environments. The open frame wall rack's mounting holes are positioned 16in. apart, matching typical drywall construction framework to ensure simple and secure wall-stud anchoring.

Cage nuts and screws are included with the wall-mount bracket, to save you the hassle of sourcing separate mounting hardware. The bracket is ideal for mounting equipment 12" or less in depth to ensure there is room for cabling.

WALLMOUNT4 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Wall mount patch panels and other slim 19" rackmount equipment

## Features

- **4U WALL MOUNT RACK:** This 19 inch wide low profile wall mounted rack has a maximum mounting depth of 14 in [35 cm], recommended for networking equipment up to 12in deep, leaving 2in for cable routing; maximum weight capacity of 44 lbs [20kg]
- **EASY TO INSTALL:** The 4U wall mounting patch panel bracket ships fully assembled and comes complete with M6 Screws and M6 Cage Nuts for easier equipment installation, to save you the hassle of sourcing separate mounting hardware
- **COLD-ROLLED STEEL CONSTRUCTION:** The wall mounting data rack features a solid steel design for ultimate durability and to ensure a safe and sturdy mounting solution & includes wall mounting hardware; Installs onto 16" studs with mounting holes
- **EASY CABLE MANAGEMENT:** Built with efficiency in mind, the small wall mount patch panel bracket has rear cable routing access for easy cable organization in your network closet, server room, wiring closet, classroom
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; this 4U wallmount rack backed for life by StarTech.com, including free 24/5 North America based multi-lingual tech support

---

### Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	4U
Special Features	Ships Fully Assembled
	U-Markings
	Wall-Mountable
	Grounding Lug(s)
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity	44.1 lb [20 kg]
-----------------	-----------------

---

**Physical Characteristics**

Color	Black
Construction Material	Steel
Material	Steel
Product Length	13.8 in [35.0 cm]
Product Width	19.6 in [49.8 cm]
Product Height	7.2 in [18.4 cm]
Weight of Product	10.9 lb [5.0 kg]
Maximum Mounting Depth	13.8 in [35 cm]

**Packaging Information**

Package Quantity	1
Package Length	15.2 in [38.7 cm]
Package Width	21.0 in [53.4 cm]
Package Height	9.1 in [23.0 cm]
Shipping (Package) Weight	11.0 lb [5.0 kg]

**What's in the Box**

Included in Package	1 - Wall Mounting Bracket for Patch Panel
	16 - M6 Screws
	16 - M6 Cage Nuts
	16 - M6 Plastic Cup Washers
	4 - Plastic Wall Anchors
	4 - M5-25 Flat-head screws

***\*Product appearance and specifications are subject to change without notice.***