



STC-HD213SDI

HD SDI, Area Scan Camera, Full HD 1080p, Color, CMOS Sony IMX291, 1/2.8", 2.8 μm , 60 fps, Rolling Shutter, C Mount, Cased

Specifications

Camera type	Color
Number of pixels	2 MP
Interface	HD SDI
Lens mount	C-mount
Shutter type	Global
Image width	1920 pixels
Image height	1080 pixels
Image sensor format	1/2.8"
Image sensor type	Other
Pixel size	2.8 µm
Frame rate	60 fps
Optical filter	None
Lens type	N/A
Scan type	Area scan
Material housing	Aluminium A6061

Accessories



RC-HD133

Remote Control Unit for all DVI/SDI camera models

CAD Library



CLCtrl2 Software

EN ZIP 2.85 MB



Industrial Cameras STC/FS Series Brochure

EN PDF 15.7 MB



JTACtrl Software

EN ZIP 2.48 MB



LSCtrl Software

EN ZIP 1.73 MB

MacOS SDK MacOSX Sierra, Mac OSX High Sierra

Software

EN PKG 79.9 MB

SDK CentOS 7, Fedora 26, Fedora 28 (64bit / 32bit)

Software

EN TAR 53.1 MB

SDK Debian 9.4 (64bit/32bit)

Software

EN TAR 52.7 MB

SDK Raspberry PI 3 Raspbian 9

Software

EN TAR 52.1 MB

SDK Ubuntu 16.04 (ARM 64bit)

Software

EN TAR 52.5 MB

SDK Ubuntu 18.04 (64bit/32bit)

Software

EN TAR 52.7 MB

SDK ubuntu 16.04 (64bit/32bit)

Software

EN TAR 52.8 MB



SWIR Camera LBS132POE Manual Users Manual

EN PDF 2.32 MB



SWIR Camera LBS34POE Manual Users Manual

EN PDF 2.39 MB




SWIR Camera datasheet Datasheet

EN PDF 18.4 MB



Sentech SDK V1.1.2 Software

EN ZIP 572 MB



StUVC Viewer Software

EN ZIP 612 KB



USB3Vision_GIGE_CoaXPress Software

EN ZIP 252 MB

