

4-Post 18U Mobile Open Frame Server Rack, Four Post 19" Network Rack with Wheels, Rolling Rack with Adjustable Depth for Computer/AV/Data/IT Equipment - Casters, Leveling Feet or Floor Mounting

Product ID: 4POSTRACK18U



The 18U open frame rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 18U 4 post rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40 in.) that make it easy to adapt the adjustable server rack to fit your equipment.

This durable free standing server rack supports a static loading capacity of up to 1200 lb. (544 kg) and portable rolling weight capacity of 660 lb. (300 kg). The rack also features offers compliance with the EIA/ECA-310 standard for a universal design that's compatible with most network equipment rack equipment.

For a complete server storage solution that saves you time and hassle, the mobile server rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability while free standing.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Suitable for rack-mount equipment where security at the rack level is not required
- Durable storage for rack-mount servers, KVM switches, and networking equipment
- Rack-mounting A/V equipment in a radio or television studio

Features

- **ADJUSTABLE DEPTH:** 4-Post 18U open frame server rack with 4 vertical rails and adjustable mounting depth 22" to 40" (56,0cm to 101,7cm); Compatible with various servers / switches / data / AV and other IT equipment; EIA/ECA-310-E Compliant
- **EASY ASSEMBLY:** Mobile network rack with easy-to-follow assembly instructions and online video; Compact flat-pack shipping to avoid damage and facilitate installation; Only 35in (90cm) high, ideal for utility/server closets or narrow home/office spaces
- **COLD ROLLED STEEL:** Durable 4 Post 19" open frame rack designed for ventilation with 18U mounting height and 1200lb (544kg) weight capacity (stationary); 3 install options included: casters, levelling feet, or base-plate to secure rack to the floor
- **HARDWARE INCLUDED:** Rolling computer/data rack includes cage nuts and screws to mount equipment, easy to read Units (U) and depth adjustment markings, cable management hooks for organization, and required assembly tools
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 18U rack is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	18U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes

	Built-in Cable Management	
	Casters (Included)	
	Grounding Lug(s)	
	Leveling Feet	
	Easy Assembly	
	U-Markings	
	Mounting Rail Profile	L-Shape
Performance	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
<hr/>		
Physical Characteristics	Weight Capacity (Stationary)	1199.5 lb [544 kg]
	<hr/>	
	Color	Black
	Construction Material	Steel
	Product Length	44.1 in [111.9 cm]
	Product Width	23.6 in [60.0 cm]
	Product Height	35.6 in [90.4 cm]
	Weight of Product	58.4 lb [26.5 kg]
	Maximum Mounting Depth	40.0 in [101.7 cm]
	Minimum Mounting Depth	22.0 in [56 cm]
Packaging Information	Product Height with Casters	38.5 in [97.7 cm]
	<hr/>	
	Flat Pack (Assembly Required)	Yes
	Package Quantity	1

Package Length	55.9 in [142.0 cm]
Package Width	9.8 in [25.0 cm]
Package Height	5.1 in [13.0 cm]
Shipping (Package) Weight	65.7 lb [29.8 kg]

What's in the Box

Included in Package	4 - Caster
	18 - M6 Flange Nut
	18 - M6 Flat Washer
	18 - M6 Hex Screw
	8 - Cable Management Hook
	8 - Hook Mounting Screw
	2 - Left Vertical Rail
	2 - Right Vertical Rail
	8 - Corner Section
	4 - Center Section
	2 - Top Bracket
	2 - Base Bracket
	50 - M8 Hex Screw
	1 - 10mm Wrench
	1 - 13mm Wrench
	1 - Philips Head Screwdriver
	4 - Philips Head Screw
	4 - Locking Washer
	24 - M6 Screw
	24 - M6 Plastic Washer

24 - M6 Cage Nut

4 - Leveling Feet

50 - M8 Flat Washer

4 - Grounding Wire

1 - Manual

****Product appearance and specifications are subject to change without notice.***