



SIMATIC Tablet PC Entry Plus 10.1" Multitouch 256 GB SSD, 8 GB RAM Intel Core i5-11 Windows 10 IOT Enterprise LTSC resolution: 1280x800 pixels brightness: 350 cd/m² WiFi, Bluetooth 1D/2D bar code reader built-in global 4G/LTE module with 3,500 mAh battery; you must select your power supply cord

General information	
Design of the programming device	Tablet PC
Display	
Screen diagonal	10.1 in
Resolution (pixels)	
• Horizontal image resolution	1 280 pixel
• Vertical image resolution	800 pixel
General features	
• Non-reflecting	No
• Luminance	350 cd/m ²
Backlighting	
• Type of backlighting	LED
Control elements	
Keyboard fonts	
• Design	Touch
Supply voltage	
Design of the power supply	External wide-range power supply; 3-pole
Rated value (DC)	19 V
permissible range, lower limit (AC)	100 V
permissible range, upper limit (AC)	240 V
Processor	
Hyper-threading	No
Turbo Boost Technology 2.0	Yes
Drives	
CD-RW	No
DVD-ROM	No
DVD RW drive available	No
Hard disk	No
• Memory capacity	8 Gbyte
SSD	Yes
• Memory capacity	256 Gbyte
TPM Security Chip	Yes; 2.0 (version for China without TPM)
Memory	
Type of memory	DDR4 SO-DIMM
Work memory	
• integrated	8 Gbyte
• Number of slots	1
Accumulator	
Replaceable	Yes; Lithium-ion battery
Capacity	3 500 mA·h

Battery runtime, min.	6 h
Hardware configuration	
Slots	
• Number of ExpressCard slots	0
Interfaces	
Number of industrial Ethernet interfaces	1
Number of interfaces PROFIBUS DP	0
Number of RS 232 interfaces	0
Number of USB interfaces	2
• Type A	1
• Type C	1
MPI	No
Bluetooth radio standard	Yes
Universal Audio Jack	Yes
Video interfaces	
• analog video signal (VGA)	No
• DVI-I	No
• DisplayPort	No
• Micro HDMI	Yes
Industrial Ethernet	
• Industrial Ethernet interface	1x Ethernet (RJ45)
— 100 Mbps	Yes
— 1000 Mbps	Yes
• Wake on LAN	No
• IAMT (Intel Active Management Technology)	No
EMC	
Interference immunity against discharge of static electricity	
• Interference immunity against discharge of static electricity acc. to IEC 61000-4-2	Yes
Degree and class of protection	
IP degree of protection	IP65
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
FCC	Yes
DIN/ISO 9001	No
Military use	
• Conforms to MIL-STD-810G	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	45 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Relative humidity	
• Operation, min.	50 %
• Operation, max.	95 %
Vibrations	
• Operation, tested according to IEC 60068-2-6	Yes
Shock testing	
• tested according to IEC 60068-2-27	Yes
• tested according to IEC 60068-2-29	No
Operating systems	
Local language of operating system	Multi-Language User Interface (MUI): 6 languages (English, German, French, Spanish, Italian, Chinese)
pre-installed operating system	
• Windows 10	Yes
Software	
Preinstalled	

- STEP 7 Professional 2010
- STEP 7 Professional (TIA Portal)
- STEP 7
- WinCC flexible Advanced 2008
- WinCC Advanced (TIA Portal)
- STEP 5

No
No
No
No
No
No

Mechanics/material

Material of housing	plastic
Handle	No
Socket for Kensington lock	Yes
rubber corner guards	Yes

Dimensions

Width	272 mm
Height	25 mm
Depth	192 mm

Weights

Weight, approx.	1.1 kg
-----------------	--------

Scope of supply

Accumulator	Yes
Power supply	Yes
Backpack	No
SIMATIC Software	No
Recovery media	No; Restore & Recovery

Other

free hotline	Yes
--------------	-----

last modified: 9/11/2023 