

## UL PICCOLO UL PC M 95 T



Sample photo

**Order symbol:** UL PC M 95 T  
**Product nbr:** 8714018  
**Description:** UL Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074038982  
**El. number:**  
**Finland:**  
**Electric No. Denmark:** 8212031209  
**Electric No. Italy:** 7202060U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		230	140	95	Ingress Protection (EN 60529): IP66/IP67
inch:		9.1	5.5	3.7	Impact Resistance (EN 62262): IK08
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>	Polycarbonate				Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>	RAL 7035 -light grey				UV resistance: UL 508
<b>Cover screws material:</b>	Polyamide				Flammability Rating: UL 746C 5"
<b>Cover colour:</b>	Clear transparent				UL Type:
<b>Cover screws colour:</b>	Grey				Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>	Polyurethane				
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Temperature °C (short term):</b>	-40 ... 120 °C				Underwriters Laboratories
<b>Temperature °C (continuous):</b>	-40 ... 80 °C				SGS Fimko
<b>Temperature °F (short term):</b>	-40 ... 250 °F				UL Canada
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				Gost R

PICCOLO 230x140x95-125

