

Product data sheet

Specifications



outlet grille plast cut out 125x125mm
ext dim 137x117mm IP54

NSYCAG125LPF

Main

Range	ClimaSys
Product	ClimaSys CA
Range compatibility	ClimaSys (ClimaSys CV) fan
Product or component type	Outlet grille
Accessory / separate part category	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Fixing mode	Clipped By screws
Device composition	1 support frame 1 external part 1 G2 M1 synthetic standard filter

Complementary

Material	Injected thermoplastic (ASA PC)
Colour	External part: grey (RAL 7035)
Cut-out dimensions	125 x 125 mm
Height	170 mm external:
Width	150 mm external:
Depth	15 mm external:

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	15.5 cm
Package 1 Length	18 cm
Package 1 Weight	220 g
Unit Type of Package 2	CAR
Number of Units in Package 2	56
Package 2 Height	38.5 cm

Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	13 kg
Unit Type of Package 3	P12
Number of Units in Package 3	448
Package 3 Height	91 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	119 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)