

Eaton PDD32F0225TFAN

Catalog Number: PDD32F0225TFAN

Power Defense UL/CSA 240V Max, Frame 3, Two Pole, 225A, 35kA/240V, T-M (Fxd-Adj) TU, No Terminals

General specifications

Product Name	Catalog Number
Eaton Power Defense molded case circuit breaker	PDD32F0225TFAN
	UPC
	786679850152
Product Length/Depth	Product Height
109.1 mm	257.1 mm
Product Width	Product Weight
138.9 mm	5.2163 kg
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL 489
	CSA



Delivery program

Amperage Rating

225 A

Circuit breaker frame type

Complete breaker

Frame

3

Number of poles

Two-pole

General information

Circuit breaker type

PD3 UL/CSA Only

Class

Class A

Trip Type

T-M (Fxd-Adj) TU

Technical data - Electrical

Voltage rating

240 V AC

Voltage rating - max

240 V

Technical data - Mechanical - Terminals

Terminals

No Terminals

Technical information

Interrupt rating

35 kAIC at 240 Vac

Interrupt rating range

35 kAIC @240V (UL)

10 kAIC Icu @250 Vdc

Resources

3D CAD drawing package

[Eaton Power Defense PDD32F0225TFAN 3D drawing](#)

Application notes

[Consulting application guide - molded case circuit breakers](#)

Brochures

[StrandAble terminals product aid](#)

[Power Defense molded case circuit breaker selection poster](#)

[Power Defense brochure](#)

[Power Defense technical selling booklet](#)

Catalogs

[Molded case circuit breakers catalog](#)

Certification reports

[PDG3 UL authorization 100-400a](#)

[PDG3 UL authorization 250-600a TMTU](#)

[Power Defense Declaration concerning California's Proposition 65](#)

Installation instructions

[Power Defense Frame 3 Breaker Instructions \(IL012107EN\).pdf](#)

Multimedia

[Power Defense Frame 3 Variable Depth Rotary Handle Mechanism](#)

[Installation How-To Video](#)

[Power Defense Frame 5 Trip Unit How-To Video](#)

[Eaton Power Defense for superior arc flash safety](#)

[Power Defense Frame 2 Variable Depth Rotary Handle Mechanism](#)

[Installation How-To Video](#)

[Power Defense molded case circuit breakers](#)

[Power Defense Frame 6 Trip Unit How-To Video](#)

[Power Defense Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - PDD32F0225TFAN](#)

Time/current curves

[Power Defense time current curve Frame 3 - PD3](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

White papers

[Molded case and low-voltage breaker health](#)

[Safer by design: arc energy reduction techniques](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia