

SIMATIC IPC MD-34A 2-bay battery charger; you must select your power supply cord

General information	
Design of the programming device	Tablet PC Accessory
Supply voltage	
Rated value (DC)	19 V
permissible range, lower limit (AC)	100 V
permissible range, upper limit (AC)	240 V
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	45 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Relative humidity	
• Operation, min.	50 %
• Operation, max.	95 %
Dimensions	
Width	216 mm
Height	81 mm
Depth	50 mm
Weights	
Weight, approx.	340 mg

last modified: 10/23/2023 