



## Modular Plugs

A complete variety of UL Recognized modular plugs are available. All plugs have 15 micro inches\* of gold plating on the contacts which meet all standard applications for voice and data. Flat satin stranded, round stranded, and round solid cables are accommodated. Keyed, MMJ, DEC types, shielded and category 5 versions are available. Flat modular cable types accept 24-28 AWG, stranded. Round cable types accept 24-26 AWG, stranded or solid.

Part No.	ROHS	Description	Ty
300062	☑	4P4C Handset Plug For Flat Satin, Stranded	—
300064	☑	6P4C Plug For Flat Satin, Stranded	RJ11
300066	☑	6P6C Plug For Flat Satin, Stranded	RJ12
300068	☑	8P8C Plug For Flat Satin, Stranded	RJ45
300164	☑	6P4C Plug For Round Twisted Pair, Solid	RJ11
300166	☑	6P6C Plug For Round Twisted Pair, Solid	RJ12
300168	☑	8P8C Plug For Round Twisted Pair, Solid	RJ45
300168K	☑	8P8C Keyed Plug For Round Twisted Pair, Solid	RJ45
300160	☑	<b>DISCONTINUED</b>	RJ50
300264	☑	6P4C Plug For Round Twisted Pair, Stranded	RJ11
300266	☑	6P6C Plug For Round Twisted Pair, Stranded	RJ12
300268	☑	8P8C Plug For Round Twisted Pair, Stranded	RJ45
300066D	☑	6P6C DEC Offset Plug For Flat Satin	MMJ
300068K	☑	8P8C Keyed Plug For Round Twisted Pair, Stranded	RJ45
300068S	☑	8P8C Shielded Plug For Round Twisted Pair, Solid <b>DISCONTINUED</b>	RJ45
300568	☑	8P8C Category 5 Plug For Round Twisted Pair, Solid	RJ45
300566EZ	☑	6P6C EZ-RJ12 Plug (see below)	RJ12
300568EZ	☑	8P8C EZ-RJ45 Category 5 Plug (see below)	RJ45
300568L	☑	8P8C Category 5 Liner Plug For Round Twisted Pair, Solid	RJ45
300568S	☑	8P8C Shielded Category 5 Liner Plug For Round, Solid	RJ45
300668EZ	☑	8P8C EZ-RJ45 Category 6 Plug <b>NEW</b> (see below)	RJ45
300668SEZ	☑	8P8C EZ-RJ45 Shielded Category 6 Plug <b>NEW</b> (see below)	RJ45
CXB300EZ	☑	Category 6 Boot with Strain Relief	Boot

