



Standard BNC Connectors

Bomar's true 75 ohm BNC connectors fit all standard broadcast cables in addition to standard RG cables utilizing standard existing tooling. Made from precision machined brass, these rugged connectors maintain excellent return loss in analog and serial digital applications. 50 Ohm versions also available. Precision matched for each cable. The SBC number identifies the cable manufacturer's part number. An easy choice.



Part Number	Fits Cable	RG Type
SBC1164B	1164B	-----
SBC1167B	1167B	-----
SBC1407B	1407B	-----
SBC1426	1426	-----
SBC1505A	1505A	RG59(20awg)
SBC1506A	1506A	RG59 Plen
SBC1520A	1520A	RG179
SBC1694A	1694A	RG6(18awg)
SBC1695A	1695A	RG6 Plen
SBC1855A	1855A	-----

Connectors for many other cable part numbers available.

Part Number	Fits Cable	RG Type
SBC1865A	1865A	-----
SBC5565	5565	RG59(20awg)
SBC5765	5765	RG6
SBC7731A	7731A	RG11(14awg)
SBC8218	8218	-----
SBC8241	8241(A)	RG59(23awg)
SBC8281	8281	RG59 Dbl Shd
SBC83264	83264	RG179
SBC9221	9221	RG179
SBC9259	9259	RG59(22awg)

Installer Kits are convenient covered trays that contain fifty of one particular BNC connector. Ideal for installations where you need to move from one area to another.



Easy visibility as to how many you have left. And no small bag to open. For added convenience, each kit contains two extra pins and two extra ferrules. Kits are available for some of the most popular numbers. Others available upon special order.

Part Number	Fits Cable
SBC1505A	1505A
SBC1694A	1694A
SBC1855A	1655A
SBC8218	8218
SBC8241	8241
SBC8281	8281
HBC1505A*	1505A
HBC1694A*	1694A
HBC1855A*	1855A
*High definition	