75 Ohm Coax

Product Number: B-8241F-G8M-1000

This PDF file was generated by interstatewire.com. Questions? Call us at (800).527.0010

22 AWG stranded (7x30) .030 bare copper conductor. Foam polyethylene insulation. Bare copper braid shield (95% coverage). PVC jacket.

Specifications

Temp Rating, Non-UL	60ºC
Temp Range, Operating	-30ºC To +60ºC
Capacitance	17.300
Capacitance (Metric)	56.7613
Delay	1.30
Impedance	75
Inductance	.090
Inductance (Metric)	0.29529
Voltage, Max. Operating	300 V RMS
Velocity of Propagation (%)	78
RoHS	Yes
Weight	36.0000
Coaxial Type	59/U
Conductor Size (AWG)	22
Conductor Material	BC - Bare Copper
Conductor Diameter	.0300
Number of Coax	1
Conductor Stranding	7x30
Insulation Material	FPE - Foam Polyethylene
Overall Nominal Diameter	.242
Outer Jacket Material	PVC - Polyvinyl Chloride
Outer Shield Coverage	95
Outer Shield Material	BC - Bare Copper
Outer Shield Type	Braid

Amount	1000 ea
Conductor - Diameter (Metric)	0.762
Overall Cabling - Overall Nominal Diameter (Metric	6.1468
SKU	B-8241F-G8M-1000
Manufacturer	Belden
Mfr. Part No	8241F G8M1000
Туре	Coax