



Quick Drill

- [Certified Green](#)
- [HID Lamps](#)
- [Fluorescent Lamps](#)
- [Halogen Lamps](#)
- [Incandescent Lamps](#)
- [Safety-Coated Lamps](#)
- [Energy Efficient Systems](#)
- [LED Lamps](#)
- [Miniature & Automotive Lamps](#)
- [Automotive Forward Lighting](#)
- [Sealed Beam Lamps](#)
- [ANSI Coded Lamps](#)
- [Photographic & SSTV Lamps](#)
- [ArcMaster SSTV Discharge Lamps](#)
- [ColorMaster Digital Imaging Lamps](#)
- [Germicidal Lamps](#)
- [Healthcare, Medical & Scientific Lamps](#)
- [LCD Lamps](#)

Information

- [FAQS](#)
- [Literature](#)
- [Events](#)
- [New Products](#)
- [News](#)
- [SoLux](#)
- [Industry Memberships](#)

**For great deals on  
excess inventory!!**

Call  
1-800-852-2217

[JCD12V10WH20](#)

[<< Previous Page](#)

[Print Page](#)  
[Print Spec Sheet](#)

**ITEM NO: JCD12V10WH20**



**Item Description:**

10W 12V T2-3/4 G4 Base

**General**

Lamp No	JCD12V10WH20
Bar Code	15007
Volts	12
Watts	10
Lumens	150
Filament	C-6
MOL in/mm	1.22/31.0
MOD in/mm	0.36/9.0
Avg Life	2000
Bulb	T-2 3/4
Base	G4 (Sub-Miniature 2-Pin)
LCL in/mm	0.79/20.0
Watts Amps	10
CT deg K	2900
Type Use	General
Common Code	64415 / JC12V10WGG1

**Partner Login**

User:

Pass:

Remember Me