



Quick Drill

- [Certified Green](#)
- [HID Lamps](#)
- [Fluorescent Lamps](#)
- [Halogen Lamps](#)
- [Incandescent Lamps](#)
- [Safety-Coated Lamps](#)
- [Energy Efficient Systems](#)
- [LED Lamps](#)
- [Miniature & Automotive Lamps](#)
- [Automotive Forward Lighting](#)
- [Sealed Beam Lamps](#)
- [ANSI Coded Lamps](#)
- [Photographic & SSTV Lamps](#)
- [ArcMaster SSTV Discharge Lamps](#)
- [ColorMaster Digital Imaging Lamps](#)
- [Germicidal Lamps](#)
- [Healthcare, Medical & Scientific Lamps](#)
- [LCD Lamps](#)

Information

- [FAQS](#)
- [Literature](#)
- [Events](#)
- [New Products](#)
- [News](#)
- [SoLux](#)
- [Industry Memberships](#)

For great deals on
excess inventory!!

Call
1-800-852-2217

➔ [JC12V20WH20](#)

[<< Previous Page](#)

[Print Page](#)
[Print Spec Sheet](#)

Partner Login

User:

Pass:

Remember Me

ITEM NO: JC12V20WH20



Item Description:

12V 20W T-3 G6.35 Base

General

Lamp No	JC12V20WH20
Bar Code	15013
Volts	12
Watts	20
Lumens	350
Filament	C-6
Coating	Clear
MOL in/mm	1.73/44.0
MOD in/mm	0.46/11.5
Avg Life	2000
Bulb	T-3
Base	G6.35
LCL in/mm	1.18/30.0
Watts Amps	20
CT deg K	2850
Type Use	General
Common Code	JC12V20WGG2