Cable construction PVC

- Partly oil and chemical proofEspecially suited for dry areas

	Color code	Conductors	Cable ja	ncket
			Ø mm	material
Cable 01	Brown, blue, black	3 x 0,34 mm ² (AWG 22)	5	PVC
Cable 02	Brown, white, blue, black	4 x 0,34 mm² (AWG 22)	5	PVC
Cable 03	Brown, white, blue, black, grey	5 x 0,34 mm ² (AWG 22)	5	PVC
Cable 07	Brown, blue, black	3 x 0,34 mm ² (AWG 22)	5	PVC shielded
Cable 08	Brown, white, blue, black	4 x 0,34 mm² (AWG 22)	5	PVC shielded
Cable 09	Brown, white, blue, black, grey	5 x 0,34 mm² (AWG 22)	5	PVC shielded

Cable construction PUR

- Very good oil and chemical resistance
- Especially suited for applications in the machine and installation area with rough environments, also in the food industry


	Color code	Conductors	Cable ja	ncket
			Ø mm	material
Cable 04	Brown, blue, black	3 x 0,34 mm ² (AWG 22)	5	PUR
Cable 05	Brown, white, blue, black	4 x 0,34 mm² (AWG 22)	5	PUR
Cable 06	Brown, white, blue, black, grey	5 x 0,34 mm ² (AWG 22)	5	PUR
Cable 10	Brown, blue, black	3 x 0,34 mm ² (AWG 22)	5	PUR shielded
Cable 11	Brown, white, blue, black	4 x 0,34 mm² (AWG 22)	5	PUR shielded
Cable 12	Brown, white, blue, black, grey	5 x 0,34 mm² (AWG 22)	5	PUR shielded

Ordering example for different cable lengths

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths upon request. Minimum order quantities will apply.



Male cable connector, straight with anti-vibration coupling nut



Contacts	Cable jacket	Order No.
3	PVC	C112 10A01310
	PUR	C112 10A04310
4	PVC	C112 10A02410
	PUR	C112 10A05410
5	PVC	C112 10A03510
	PUR	C112 10A06510

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths and coding upon request.

Contact arrangement

3 contacts

4 contacts

5 contacts










first mate – last break 2




Male cable connector, right angled with anti-vibration coupling nut



Contacts	Cable jacket	Order No.
3	PVC	C112 10B01310
	PUR	C112 10B04310
4	PVC	C112 10B02410
	PUR	C112 10B05410
5	PVC	C112 10B03510
	PUR	C112 10B06510

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths and coding upon request.



3 contacts

4 contacts

5 contacts










first mate - last break 2



Female cable connector, straight with anti-vibration coupling nut



Contacts	Cable jacket	Order No.
3	PVC	C112 10C01310
	PUR	C112 10C04310
4	PVC	C112 10C02410
	PUR	C112 10C05410
5	PVC	C112 10C03510
	PUR	C112 10C06510

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths and coding upon request.

Contact arrangement

3 contacts

4 contacts

5 contacts












Female cable connector, right angled

with anti-vibration coupling nut



Contacts	Cable jacket	Order No.
3	PVC	C112 10D01310
	PUR	C112 10D04310
4	PVC	C112 10D02410
	PUR	C112 10D05410
5	PVC	C112 10D03510
	PUR	C112 10D06510

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths and coding upon request.

Contact arrangement

3 contacts

4 contacts

5 contacts












Male cable connector, straight, shielded with anti-vibration coupling nut



Contacts	Cable jacket	Order No.
3	PVC	C112 11A07310
	PUR	C112 11A10310
4	PVC	C112 11A08410
	PUR	C112 11A11410
5	PVC	C112 11A09510
	PUR	C112 11A12510

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths and coding upon request.

Contact arrangement

3 contacts

4 contacts

5 contacts













Male cable connector, right angled, shielded with anti-vibration coupling nut



Contacts	Cable jacket	Order No.
3	PVC	C112 11B07310
	PUR	C112 11B10310
4	PVC	C112 11B08410
	PUR	C112 11B11410
5	PVC	C112 11B09510
	PUR	C112 11B12510

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths and coding upon request.



3 contacts

4 contacts

5 contacts










first mate - last break 2



Female cable connector, straight, shielded with anti-vibration coupling nut



Contacts	Cable jacket	Order No.
3	PVC	C112 11C07310
	PUR	C112 11C10310
4	PVC	C112 11C08410
	PUR	C112 11C11410
5	PVC	C112 11C09510
	PUR	C112 11C12510

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths and coding upon request.

Contact arrangement

3 contacts

4 contacts

5 contacts












Female cable connector, right angled, shielded with anti-vibration coupling nut



Contacts	Cable jacket	Order No.
3	PVC	C112 11D07310
	PUR	C112 11D10310
4	PVC	C112 11D08410
	PUR	C112 11D11410
5	PVC	C112 11D09510
	PUR	C112 11D12510

Standard cable lengths: 2 m and 5 m. Non-standard cable lengths and coding upon request.

Contact arrangement

3 contacts

4 contacts

5 contacts







