

ELECTRONIC HEAT GUNS

Introducing a new generation of STEINEL electronic heat guns.

STEINEL heat guns have built a reputation for using state of the art technology to maximize precision and durability. Our new generation of heat guns incorporates exciting new features responding directly to ever increasing global requirements for rigorous, formalized quality control.

HG 2510 ESD

ESD Safe Programmable IntelliTemp™ Heat Gun

ESD safe programmable heat gun with LOC Lockable Override Control™ of temperature and airflow output settings. LCD display enables temperature selection in 10°F increments.

Temperature	Continuously variable 120 - 1200 °F
Airflow	3.6 - 17.6 CFM
Switch	1) Cool Air Stage (120°F / 3.6 CFM) 2) Variable Temp & Airflow
Programs	Four customizable pre-set temperature/airflow programs
Output	1600 watts
Voltage	120 VAC / 60 Hz
Weight	33 oz
Warranty	One year limited
Item Number	34890
Accessories	Accepts a full range of nozzles and accessories.



Available with or without a heavy duty carrying case.

HG 2310 LCD

Programmable IntelliTemp™ Heat Gun with LCD Display

Programmable heat gun with LOC Lockable Override Control™ of temperature and airflow output settings. LCD display enables temperature selection in 10°F increments.

Temperature	Continuously variable 120 - 1200 °F
Airflow	3.6 - 17.6 CFM
Switch	1) Cool Air Stage (120°F / 3.6 CFM) 2) Variable Temp & Airflow
Programs	Four customizable pre-set temperature/airflow programs
Output	1600 watts
Voltage	120 VAC / 60 Hz
Weight	33 oz
Warranty	One year limited
Item Number	34870
Kits	Available in industry specific kit presentations.
Accessories	Accepts a full range of nozzles and accessories.



Available with or without a heavy duty carrying case.

HL 2010 E

IntelliTemp™ Heat Gun with LCD Temperature Display

Microprocessor controlled heat gun with LCD display enabling temperature selection in 10°F increments. STEINEL's exclusive DuraTherm™ heating element ensures long life and even heat.

Temperature	Continuously variable 120 - 1150 °F
Airflow	3.6 / 10.6 / 17.6 CFM
Switch	1) Cool Air (120°F / 3.6 CFM) 2) Var Temp/10.6 CFM 3) Var Temp/17.6 CFM
Output	1500 watts
Voltage	120 VAC / 60 Hz
Weight	30 oz
Warranty	One year limited
Item Number	34850
▶ Kits	Available in industry specific kit presentations.
▶ Accessories	Accepts a full range of nozzles and accessories.



Available with or without a heavy duty carrying case.

HL 1910 E

Variable Temperature Electronic Heat Gun

Powerful heat gun with variable temperature and electronic thermocouple control for flexible use and maximum reliability. STEINEL's exclusive DuraTherm™ heating element ensures long life and even heat.

Temperature	Continuously variable 120°F - 1100°F
Airflow	3.6 / 10.6 / 17.6 CFM
Switch	1) 120°F / 3.6 CFM 2) Var Temp/10.6 CFM 2) Var Temp/17.6 CFM
Output	1500 watts
Voltage	120 VAC / 60 Hz
Weight	30 oz
Warranty	One year limited
Item Number	34830
▶ Kits	Available in industry specific kit presentations.
▶ Accessories	Accepts a full range of nozzles and accessories.



Available with or without a heavy duty carrying case.

HG 2000 E

Electronic Heat Gun

Ergonomic, electronically controlled heat gun.

Temperature	Continuously variable 120°F - 1100°F
Airflow	14.8 CFM
Output	1500 watts
Voltage	120 VAC / 60 Hz
Warranty	One year limited
Item Number	34261
▶ Kits	Available in industry specific kit presentations.
▶ Accessories	Accepts a full range of nozzles and accessories.

Available with or without a heavy duty carrying case.

STEINEL