

Series 61



Front size	18 mm dia. 18 x 18 mm 18 x 24 mm 24 mm dia. 24 x 24 mm 24 x 30 mm 25 mm dia. 26 x 26 mm 27 mm dia. 32 mm dia. 40 mm dia.
Front protection	IP 65
Mounting hole size	16 mm dia. 21 x 21 mm 21 x 27 mm 22.5 mm dia.
Switching System	Slow-make switching element Snap-action switching element
Switch rating	250 VAC, 5 A 42 VAC, 100 mA
Illumination	Filament lamp LED