## Amphenol<sup>®</sup>Connex

A New Kind of RF Solution

Products Site Tools RF Made Simple Distributors About Us News Room Contact Us Login 📜 Shopping Cart **Our Products** Search Results for: Straight Crimp Plug - Captive Contact - Standard Cable 7/16 Please note: Images are for reference only BNC D-Sub Part Number: 112508 Cable Group: 08 FME Family/Series: BNC Coaxial Connectors Finish: Nickel MCX Product Type: PLUG CRIMP Insulation: Delrin MMCX ATTACHMENTS FOR FLEXIBLE CABLE Impedance: 75 ohms SMA Description: Straight Crimp Plug -Crimp Tool: E SMB Captive Contact - Standard Cable \* Center contact .053" diameter, SMC Brass Shell 30µ" Au. True 75 ohm. Use .044 hex TNC Cable: 6/143/212/B3092/B3903 \*\* or 12-indent crimp Twin BNC Type F Type N Add to Cart | Product Specs | Customer Drawing UHF **Between-Series Adapters Shielded Terminations** Strain-Relief Boots Tools **View All Products** Copyright  $\ensuremath{\textcircled{O}}$  2001 - 2005 Amphenol Connex. All rights reserved. Copyright | Terms & Conditions | Contact Us | AmphenoIRF.com