Amphenol[®]Connex

A New Kind of RF Solution

Products Site Tools RF Made Simple Distributors About Us News Room Contact Us Login

🐺 Shopping Cart

Our Products -----<u>7/16</u> **BNC** D-Sub <u>FME</u> <u>MCX</u> **MMCX** <u>SMA</u> <u>SMB</u> <u>SMC</u> TNC Twin BNC Type F Type N <u>UHF</u> -----**Between-Series Adapters Shielded Terminations** Strain-Relief Boots Tools -----View All Products

Search Results for: Bulkhead Receptacle Jack

Please note: Images are for reference only



Part Number: 122332 Family/Series: TNC Coaxial Connectors Product Type: BULKHEAD RECEPTACLE/SOLDER POT TERMINALS Description: Bulkhead Receptacle Jack L1 = 3.2 [.126] panel thickness, L = 26.7 [1.05] Cable: Non Applicable **

Add to Cart | Product Specs | Customer Drawing

Cable Group: N/A Finish: Nickel Insulation: Delrin Impedance: 50 ohms Crimp Tool: N/A

Copyright © 2001 - 2005 Amphenol Connex. All rights reserved.