



Front size 18 mm dia.

18 x 18 mm 18 x 24 mm 24 mm dia. 24 x 24 mm 24 x 30 mm 25 mm dia. 26 x 26 mm 27 mm dia. 32 mm dia. 40 mm dia.

Front protection IP 65

Mounting hole size

16 mm dia. 21 x 21 mm 21 x 27 mm 22.5 mm dia.

Switching System

Slow-make switching element Snap-action switching element

Switch rating

250 VAC, 5 A 42 VAC, 100 mA

Illumination

Filament lamp LED











Choose one component from each of the colored sections to assemble a complete switch. For other options or further information please contact EAO Switch directly.


Product Profile

The Series 61 is a high quality, modular switch range that includes pushbuttons, indicators, selector switches, keylock switches and Emergency-stops. Available in raised or flush mount.

Self cleaning snap-action and slowmake switching elements available.

Technical drawings see pages 67-68

- IP65 Protection
- Switch Rating, 5A, 250VAC
- · Raised Mounting into 16mm cut out
- Flush Mounting into 22.5mm, 21x21mm and 21x27mm cut out
- Illumination using midget-grooved T-13/4 lamps or single chip LED's
- All standard lenses are transparent with translucent white diffusers and are available in different colors
- For keylock switches 135 different key codes are available




A guide to ordering parts choice of front bezel determines front shape for flush mount versions.

Accessories are optional.

For a complete indicator you will need to order the appropriate indicator, LED, lens and bezel (for flush mount only)



For a complete illuminated pushbutton you will need to order the appropriate actuator, contact block, LED, lens and bezel (for flush mount only)





For a complete selector switch you will need to order the appropriate actuator, contact block, LED, lever and bezel (for flush mount only)

Series 61 22.5mm 21 x 21mm 21 x 27mm 16mm IP65 5A **250VAC**

> Choose one component from each of the colored sections to assemble a complete switch. For other options or further information please contact EAO Switch directly.



Illuminated pushbutton









Universal indicator body for flush mount,

Illuminated pushbutton actuator, raised, round, square and rectangular, black plastic, 16mm mounting

Image	Part No.	Size	Part No.	Image	Part No.	Action	Size
1	61-0050.02	24 x 24mm	61-0000.02	1	61-1150.0	Momentary	24 x 24mm
2	61-0030.02	18 x 24mm		1	61-1250.0	Maintained	24 x 24mm
3	61-0020.02	18 x 18mm		2	61-1130.0	Momentary	18 x 24mm
4	61-0010.02	18mm Ø		2	61-1230.0	Maintained	18 x 24mm
				3	61-1120-0	Momentary	18 x 18mm
				3	61-1220.0	Maintained	18 x 18mm
				4	61-1110.0	Momentary	18mm Ø
				4	61-1210.0	Maintained	18mm Ø
			Flush mount adapter determin	es round,			
			square or rectangular				

For complete switch also order $\begin{tabular}{l} \begin{tabular}{l} \begin{tabular}{l}$

O: Indicator



For complete switch also order 🎖 🛕



For complete switch also order 🕢 🍟 🛕








Universal illuminated flush mount pushbutton actuator, round, black plastic

Part No.	Action		
61-1100.0	Momentary		
61-1200.0	Maintained		
Flush mount adapter determines round,			
square or rectangular			











61 Indicator

Raised, Round, Square, Rectangular




61 Indicator

Flush, Round, Square, Rectangular




61 Pushbutton

Illuminated, Raised, Round, Square, Rectangular




61 Pushbutton

Illuminated, Flush, Round, Square, Rectangular



61 Keylock

2 & 3-Position, Round, Square, Rectangular



61 Selector

2 & 3-Position, Round, Square, Rectangular

