


REV.	DATE	ECR NO.	DESCRIPTION
NC	02/03/09	-	INITIAL RELEASE



LENGTH TABLE	
PART NUMBER	LENGTH (IN.)
135101-01-06.00	6.00
135101-01-12.00	12.00
135101-01-24.00	24.00
135101-01-36.00	36.00

- NOTE:
1. PERFORM CONTINUITY AND HI-POT TESTING.
  2. PACKAGED INDIVIDUALLY IN HEAT SEALED POLY BAG.

3	009-954-341	HEAT SHRINK TUBING, BLACK, 3/16" DIAMETER	A/R FT
2	009-881-205	COAXIAL CABLE, RG316/U	A/R FT
1	132114	CONNECTOR, SMA STRAIGHT PLUG, GOLD	2
	PN	DESCRIPTION	QTY

APPROVALS		DATE
DRAWN	G. R. S.	02/03/09
CHECKED		
ISSUED		
SHEET	1 OF 1	
CAD FILE		
C:/135/135101-01-XX.XX.DWG		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:		
0.5 - 8mm ± 0.20mm		
8 - 30mm ± 0.40mm		
30 - 120mm ± 0.50mm		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:		
.020 - .315 = ± 0.007"		
.315 - 1.180 = ± 0.015"		
1.180 - 4.724 = ± 0.020"		
DO NOT SCALE DRAWING		
PART DESCRIPTION		
SMA PLUG TO SMA PLUG, RG316		
PART NO.		
135101-01-XX.XX		
DWG. NO.	REV. NC	SCALE NA
135101-01-XX.XX.DWG		A

**Amphenol Connex**