TURCK Industrial Connectivity Products



3 and 4-Pin *minifast*[®] Field Wireable Connectors

- Straight Female Connectors
- NEMA 1, 3, 4, 6P
- IEC IP 67 Protection



Drawing	Part Number	Specs	Application	Pinout
B 41 *1.065 [27.0] 7/8-16UN ************************************	B 4131-0/9	Glass filled nylon PG 9 cable gland, accepts 6-8 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 12 A	Mates with all 3-pin cordsets and receptacles	2 3
	B 4131-0/13.5	Glass filled nylon PG 13.5 cable gland, accepts 10-12 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 12 A	Mates with all 3-pin cordsets and receptacles	
	B 4141-0/9	Glass filled nylon PG 9 cable gland, accepts 6-8 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 4-pin cordsets and receptacles	2 3 1 4
	B 4141-0/13.5	Glass filled nylon PG 13.5 cable gland, accepts 10-12 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 4-pin cordsets and receptacles	