



FEMALE END VIEW



SPECIFICATIONS

CONTACT MATERIAL/PLATING	GOLD-PLATED BRASS
COUPLING NUT MATERIAL/PLATING	NICKEL-PLATED BRASS
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	125 V
MAXIMUM WIRE SIZE	18 AWG
CABLE GRIP RANGE	6-8mm
TEMPERATURE RATING	-40°C to +85°C (-40°F to +185°F)
PROTECTION CLASS	IEC IP67
SPACINGS	to VDE 0110 GROUP C
WIRE TERMINATION	SCREW TERMINAL

NOTE
PRELIMINARY
SPECIFICATIONS

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<div>TURCK INC</div> <div>High Technology Sensors and Automation Controls</div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</div>			
1. 2. 3. 4.				DRFT JBJ		DATE 07/24/00		DESCRIPTION CMB 8241-0	
				DSGN		SCALE 1=1.0			
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO. U6112-0		REV P4	
SEE SPECIFICATIONS									
FINISH		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		FILE: EURO-FW\U6112-0		SHEET 1 OF 1	
SEE SPECIFICATIONS									

ALL METAL SHIELDED FIELD WIREABLE CONNECTOR

P4	UPDATE DIMS AND SPECS	JB	10/19/00	
REV	DESCRIPTION	BY	DATE	ECO NO.