



MALE END VIEW



SPECIFICATIONS


HOUSING MATERIAL/PLATING	NYLON/BLACK
CONTACT MATERIAL/PLATING	GOLD-PLATED BRASS
COUPLING NUT MATERIAL/PLATING	NICKEL-PLATED BRASS
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	75 VDC/60 VAC
MAXIMUM WIRE SIZE	24 AWG
CABLE GRIP RANGE	3-5mm
TEMPERATURE RANGE	-40°C to +85°C (-40°F to +185°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67



RELATED DOCUMENTS

- 1.
- 2.
- 3.
- 4.

3RD ANGLE PROJECTION



THIS DRAWING IS
PROPERTY OF
TURCK INC. USE OF
THIS DOCUMENT
WITHOUT WRITTEN
PERMISSION IS
PROHIBITED.

TURCK INC
High Technology Sensors and Automation Controls

3000 CAMPUS DRIVE
MINNEAPOLIS, MN 55441
1-800-544-7769
(763) 553-7300
(763) 553-0708 fax
turck.com

MATERIAL

DRFT CBM
DSGN

DATE 05/04/99
SCALE 1=5

DESCRIPTION

BS 5231-0

FINISH

ALL DIMENSIONS
DISPLAYED ON THIS
DRAWING ARE FOR
REFERENCE ONLY

CONTACT TURCK
FOR MORE
INFORMATION

UNIT OF MEASUREMENT
MILLIMETERS

DO NOT SCALE THIS DRAWING

IDENTIFICATION NO.

U6520

REV
A

FILE: PICO-FW\U6520

SHEET 1 OF 1

A	DRAWING RELEASE	CBM	05/04/99	
REV	DESCRIPTION	BY	DATE	ECO NO.