
MALE END VIEW
6 7 1 8 3 2 1 = WHITE 2 = BROWN 3 = GREEN 4 = YELLOW 5 = GRAY 6 = PINK 7 = BLUE 8 = RED
<b>EUTO</b> Tast.

NOTES:

REV DESCRIPTION

D ADD LABEL PER ECO

1					
SPECIFICATIONS					
CONTACT CARRIER MATERIAL	NYLON OR TPU				
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW				
CONTACT MATERIAL/PLATING	BRASS/GOLD				
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL				
RATED CURRENT [A]	2.0 A				
RATED VOLTAGE [V]	60 VAC/75 VDC				
OUTER CABLE JACKET MATERIAL/COLOR	PVC/GRAY				
CONDUCTOR INSULATION MATERIAL	PVC				
NUMBER OF CONDUCTORS [AWG]	8x24 AWG				
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)				
PROTECTION CLASS	NEMA 1,3,4,6P AND IEC IP68, IP69K				



CABLE LENGTH	TOLERANCE *					
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER					
STRIP LENGTH	TOLERANCE *					
0-7mm	±0.5mm					
8-29mm	±1.0mm					
30-49mm	±2.0mm					
50-69mm	±3.0mm					
70-100mm	±4.0mm					
OVER 100mm	±5.0mm					
* UNILESS OTHERWISE SPECIFIED						

TV 01/25/18

DATE

63893

ECO NO.

## **MARNING:**

ELECTRICAL SHOCK HAZARD
CONNECTOR IS TO BE IN THE THE
MATED STATE WHILE ENERGIZED
REMOVE POWER BEFORE SERVICING.

## SOURCE DRAWING - FOR REFERENCE ONLY

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

	1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	)	MINNEAPC 1-800 (763) (763) www	AMPUS DLIS, MN D-544-7 553-7 553-0 w.turck.u	55441 7769 300 708 fax	
	MATERIAL	ALL DIMENSIONS	DRFT RWC	DATE 06/11/07 SCALE 1=1.0	DESCRIPTION RSC 8T-*-RSC 8	ВТ		
	SEE SPECIFICATIONS	DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	G ARE FOR LINIT OF MEAS		IDENTIFICATION NO.		l REV	
	FINISH	CONTACT TURCK FOR MORE	MILLIMETE	ER [INCH]	IDENTIFICATION NO.		D	
+	SEE SPECIFICATIONS	INFORMATION	DO NOT SCALE	THIS DRAWING	FILE: 777003365	SHEET	1 OF 1	