



SPECIFICATIONS				
CONTACT CARRIER MATERIAL	NYLON OR TPU			
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW			
CONTACT MATERIAL/PLATING	BRASS/GOLD			
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL			
RATED CURRENT [A]	4.0 A			
RATED VOLTAGE [V]	250 V			
OUTER JACKET MATERIAL/COLOR	TPU/GRAY			
CONDUCTOR INSULATION MATERIAL	PVC			
NUMBER OF CONDUCTORS [AWG]	4×22 AWG			
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)			
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68			
	, , , , , , , , , , , , , , , , , , , ,			





CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

## SOURCE DRAWING - FOR REFERENCE ONLY

## NOTES:

- 1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- 2. "/S90" DESIGNATES THERMOPLASTIC POLYURETHANE (TPU) CABLE.

G	ADD MALE END VIEW	RDS	02/21/12	38183
REV	DESCRIPTION	BY	DATE	ECO NO.

RELATED DOCUMENTS  1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology	Sensors and Automation Controls	3000 CAMPUS MINNEAPOLIS, MN 1-800-544- (763) 553-7 (763) 553-0 turck.com	I 55441 7769 300 708 fax
MATERIAL		DRFT CBM	DATE 10/09/00	DESCRIPTION W/Z 4 4T * DC	. 4 41 /000	
	ALL DIMENSIONS DISPLAYED ON THIS	APVD	SCALE 1=1.0	WK 4.4T-*-RS	4.41/390	
	DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT				
FINISH	NEI ENENGE ONEI			IDENTIFICATION NO.		REV
	CONTACT TURCK FOR MORE INFORMATION	MILLIMETE	ER [INCH]			G
		DO NOT SCALE	THIS DRAWING	FILE: 777000694	SHEET	1 OF 1