

## 4 and 5-Pin Field Wireable Connectors, Standard Key

- IEC IP67 Protection



Housing Style	Female Part Number	Male Part Number	Features	Pinout
<p><b>B 81..</b></p>	<p><b>B 8141-0</b> <b>B 8241-0</b></p>	<p><b>BS 8141-0</b> <b>BS 8241-0</b></p>	<p>PBT, Black, PG 7 cable gland, accepts 4-6 mm cable diameter, screw terminals, accepts up to 18 AWG conductors, 85°C, 250 V, 4 A, mates with standard key 4-pin cordsets and receptacles</p>	<p><b>Female</b></p> <p><b>Male</b></p>
<p><b>B 82..</b></p>	<p><b>B 8141-0/PG 9</b> <b>B 8241-0/PG 9</b></p>	<p><b>BS 8141-0/PG 9</b> <b>BS 8241-0/PG 9</b></p>	<p>PBT, Black, PG 9 cable gland, accepts 6-8 mm cable diameter, screw terminals, accepts up to 18 AWG conductors, 85°C, 250 V, 4 A, mates with standard key 4-pin cordsets and receptacles</p>	<p><b>Female</b></p> <p><b>Male</b></p>
<p><b>BS 81..</b></p>	<p><b>B 8151-0/PG 9</b> <b>B 8251-0/PG 9</b></p>	<p><b>BS 8151-0/PG 9</b> <b>BS 8251-0/PG 9</b></p>	<p>PBT, Black, PG 9 cable gland, accepts 4-8 mm cable diameter, screw terminals, accepts up to 18 AWG conductors, 85°C, 60 V, 4 A, mates with standard key 5-pin cordsets and receptacles</p>	<p><b>Female</b></p> <p><b>Male</b></p>
<p><b>BS 82..</b></p>	<p><b>BM 8151-0/PG 9</b></p>		<p>PBT, Black, PG 9 cable gland, accepts 6-8 mm cable diameter, screw terminals, accepts up to 18 AWG conductors, metal coupling nut, 85°C, 60 V, 4 A, mates with standard key 5-pin cordsets and receptacles</p>	<p><b>Male</b></p>

Field Wireables