

5 and 12-Pin *minifast*® Field Wireable Connectors

- Straight Female Connectors
- NEMA 1, 3, 4, 6P
- IEC IP 67 Protection



Drawing	Part Number	Specs	Application	Pinout
<p>B 41 ..</p>	B 4151-0/9	Glass filled nylon PG 9 cable gland, accepts 6-8 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	<i>Mates with all 5-pin cordsets and receptacles</i>	
	B 4151-0/13.5	Glass filled nylon PG 13.5 cable gland, accepts 10-12 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	<i>Mates with all 5-pin cordsets and receptacles</i>	
	B 4151-0/16	Glass filled nylon PG 16 cable gland, accepts 12-14 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	<i>Mates with all 5-pin cordsets and receptacles</i>	
<p>B 711 ..</p>	B 71121-0/21	Glass filled nylon accepts 18 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 600 V, 9 A	<i>Mates with all 12-pin cordsets and receptacles</i>	