TURCK

Industrial Connectivity Products



3, 4 and 5-Pin *minifast* ® Field Wireable Connectors

- Straight Male Connectors
- NEMA 1, 3, 4, 6P and IEC IP 67 Protection



Drawing Number	Part Number	Cable	Application	Pinout
BS 41 ©1.065 [27.0] 7/8-16UN 1.065 [28.0] APPROX	BS 4131-0/9	Glass filled nylon PG 9 cable gland, accepts 6-8 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85° C 250 V, 12 A	Mates with all 3-pin cordsets and receptacles	3 2 1
	BS 4131-0/13.5	Glass filled nylon PG 13.5 cable gland, accepts 10-12 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 12 A	Mates with all 3-pin cordsets and receptacles	
	BS 4141-0/9	Glass filled nylon PG 9 cable gland, accepts 6-8 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 4-pin cordsets and receptacles	1 3
	BS 4141-0/13.5	Glass filled nylon PG 13.5 cable gland, accepts 10-12 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 4-pin cordsets and receptacles	
	BS 4151-0/9	Glass filled nylon PG 9 cable gland, accepts 6-8 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 5-pin cordsets and receptacles	3 4 5
	BS 4151-0/13.5	Glass filled nylon PG 13.5 cable gland, accepts 10-12 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 5-pin cordsets and receptacles	
	BS 4151-0/16	Glass filled nylon PG 16 cable gland, accepts 12-14 mm cable diameter Screw terminals, accepts up to 16 AWG conductors 85°C 250 V, 9 A	Mates with all 5-pin cordsets and receptacles	