

Home > Product Catalog > Pump & Irrigation > Irrigation Cables > Water Resistant Fountain Cable

COMPANY

INVESTORS

## **Water Resistant Fountain Cable**



**Put-Up:** 250' (04) **Color Code:** Black (08)

**Description:** UL/CSA Listed Type SJEOOW - SJTW (TPE)

NEC Article 400 300 Volt





Part No	Description	Weight Per 1000'	Std. Pkg
23225-04-08	18/2	44	1 x 250
23325-04-08	18/3	55	1 x 250
23425-04-08	18/4	66	1 x 250
23226-04-08	16/2	54	1 x 250
23326-04-08	16/3	67	1 x 250
23426-04-08	16/4	78	1 x 250
23227-04-08	14/2	68	1 x 250
23327-04-08	14/3	84	1 x 250
23427-04-08	14/4	104	1 x 250
23228-04-08	12/2	97	1 x 250
23328-04-08	12/3	133	1 x 250
23428-04-08	12/4	157	1 x 250

## PRODUCT DATA SHEET



Controlled Document - Engineering Drive

PART NUMBER: 23326

**DESCRIPTION:** 16/3 STRANDED TYPE SJEOOW FLEXIBLE POWER CABLE

**CONSTRUCTION:** This cable consists of three bare copper insulated conductors cabled with fillers and an overall jacket.

APPROVALS: UL Standard 62, CSA 22.2 No. 49, NEC Article 400., MSHA

APPLICATION: 300V Portable Oil Resistant Submersible Outdoor Flexible Power Cable

## **Construction Parameters:**

Conductor 16 AWG Bare Copper

Stranding 26/30 Insulation Material TPE

 Insulation Thickness
 0.031" Nom.

 Insulated Conductor Diameter
 0.120" Nom.

 Number of Conductors
 3

 Lay Length
 2.00" Nom.

 Filler Type
 Polypropylene

Lay Length

Filler Type

Separator/Wrap

Jacket Material

Polypropylene
Paper Tissue
TPE

Jacket Thickness0.035" Nom.Overall Cable Diameter0.330" Nom.Approximate Cable Weight69.1 Lbs/1M' Nom.

Flame Rating UL/CSA Horizontal Flame Test

## **Electrical Properties:**

Temperature Rating -50°C to 105°C Operating Voltage 300 V RMS Max.

DC Resistance per Conductor @ 20°C 4.08 Ohms/1M' Nom.

Max Ampacity per Conductor (Per NEC Table 400-5a) 13 amps/cond (Assume two current carrying conductors)

(Note: Because of 105C temperature rating, higher current can be used under engineering supervision)

Insulation Colors Jacket Color Black White Green

Black (Other colors available for minimum order - consult factory)

Legend

CCI SEOPRENE 105 16 AWG (1.32mm²) 3/C SJEOOW E54864 (UL) 300V -50C TO 105C CSA LL39753 SJTOOW(TPE) -50C TO 105C FT2 WATER RESISTANT

(White Surface Ink Print - P-241-3-MSHA in indent)

This product complies with European Directive 2002/95/EC (RoHS)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman cable disclaims all liability in connection with the use of information contained herein or otherwise.