

PRODUCT SPECIFICATION

CATALOG NUMBER: See table below

CUSTOMER: Stock

DESCRIPTION: Push-lock SJTW extension cord with power indicator

light in the cord connector

APPROVALS: UL/CUL Listed Outdoor Use Cord Set

CONSTRUCTION PARAMETERS:

Conductor: See table below

Jacket material: PVC, see table below for color


Overall cable O.D. (nom): See table below

Cord rating: Hard Usage per the National Electric Code

Attachment plug configuration: NEMA 5-15P Cord connector configuration: NEMA 5-15R

Plug and connector material: Clear PVC, with neon power indicator lamp in the cord connector





ELECTRICAL PROPERTIES:

Cable temperature rating: -20 to +60 °C

Nominal operating voltage: 125 VAC

Maximum operating current: See table below

MARKINGS:

Cable legend type: Indent print

Catalog number	Length	Conductor	Cable color	Cable O.D. (nom)	Current rating
02327	25 ft	16/3 26/30 BC	Yellow	0.335 in	13A
02328	50 ft				
02329	100 ft				10A
02427	25 ft	14/3 41/30 BC	Yellow w/ blue stripe	0.370 in	
02418	45 ft				15A
02428	50 ft				
02419	90 ft				13A
02429	100 ft				13A
02527	25 ft	12/3 65/30 BC	Yellow w/ black stripe	0.435 in	
02518	45 ft				15A
02528	50 ft				
02519	90 ft				
02529	100 ft				

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Systems. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Systems.