Fiber Express Manager

Rack Components and Modules

AX100934 Fiber Express Manager Shelf



AX101943 Fiber*Express* Manager 1U Rack Mount Patch Panel



AX102032 Fiber*Express* Manager 1U Cable Management Accessory



AX101525 Connector Module Pre-terminated MPO-MT-RJ



Fiber Express Manager Shelf

Fiber*Express* **modules** are rack-mounted using Fiber*Express* Manager Shelves. The shelves provide the total system with extra high connection density while facilitating cable routing and patch cord management. For 19- or 23-inch rack: 19 in. shelf holds up to 12 modules; 23 in. shelf holds up to 16 modules.

Fiber Express Manager 1U

The Fiber Express Manager 1U Rack Mount Patch Panel is a low-cost, compact assembly designed for interconnection or splicing of optical fiber cables, using up to three Fiber Express Manager Modules. The low-profile design minimizes rack space to only 45 mm (1.75 in.). An optional Fiber Express Manager 1U Cable Management Accessory is also available.

Fiber Express Manager Connector Module

The Connector Module is the basic building block of the Fiber Express Manager. It is designed with a unique release mechanism that allows it to slide from the shelf like a PC card, easing management of patch cords.

	Belden Part Number			
Description	Gray	Black		
Fiber <i>Express</i> Manager				
Fiber <i>Express</i> Manager				
Shelf, 23 in., 10.9 kg (24 lb)	AX100934	AX100935		
Shelf, 19 in., 8.2 kg (18 lb)	AX101084	AX101085		
1U, Rack Mount Patch Panel, 19 in., 5 kg (11 lb) AX101944	AX101943		
1U, Cable Management Accessory, 19 in., 1 kg (2 lb) AX102033	AX102032		

Description	Belden Part Number					
	ST Type	SC Simplex	SC Duplex	SC Duplex (ST in)	LC	FC
Fiber <i>Express</i> Manager						

Fiber <i>Express</i> Manager						
Fiber Express Manager Connector	Module					
Metal Sleeve, Multimode, 6 fibers	AX101089		AX101092			
Zirconia Ceramic, Single-mode, 6 fibers	AX100936 A	X100943	AX100944			
Metal Sleeve, Multimode, 12 fibers	AX101187		AX101714	AX101120	AX101528	
Zirconia Ceramic, Single-mode, 12 fibers	AX101186		AX101713	AX101119	AX101527	
Zirconia Ceramic, Single-mode, 12 UPC pigta	ils		AX101715			
Metal Sleeve, Multimode, 24 fibers					AX102306	
Zirconia Ceramic, Single-mode, 24 fibers					AX102305	
Zirconia Ceramic, Single-mode/Multimode, 6	fibers					AX100937
	Multimode 62.5 µm	Mu	lltimode 50 µm	Single-mode		_
MDO/ms) CT towns 40 mass towns in stead	AV404400		AV404400	AV404400		·

	Multimode 62.5 µm	Multimode 50 µm	Single-mode	-
MPO(m)-ST type, 12 pre-terminated	AX101189	AX101190	AX101188	
MPO(m)-SC Duplex, 12 pre-terminated	AX101091	AX101114	AX101090	
MPO(m)-MT-RJ(m), 12 pre-terminated	AX101525	AX101526	AX101524	
MPO(m)-LC, 12 pre-terminated	AX101530	AX101531	AX101529	
MPO(m)-LC, 24 pre-terminated	AX102309	AX102308	AX102307	
MT-RJ, Beige, Multimode, 12 fibers				AX101096
MT-RJ, Blue, Single-mode, 12 fibers				AX101581

These products are in the process of being assessed for RoHS compliance. Please check our Web Site for the most current RoHS status.





DATASheet

FiberExpress Manager Shelf

Description

FiberExpress modules are rack-mounted using FiberExpress shelves. The shelves provide the total system with extra high connection density while facilitating cable routing and patch cord management. The shelves contribute to theoverall system user-friendliness in several ways which are listed below in the Features & Benefits section.

- > For 19 in. or 23 in. rack
- > 19 in. shelf holds up to 12 modules
- > 23 in. shelf holds up to 16 modules

Features & Benefits

- > Cable slack storage provided in lower portion of each shelf
- > Back door serves as working platform during connectorization
- > Cable tie-down straps provided to facilitate cable management
- > 2.54 cm (1 in.) pull-out of module allows for easy front access to connectors without potentially disconnecting other links
- > Full maintenance access at the back
- > Grounding/bonding post within each shelf
- ➤ High density- Optimizes real estate space by being able to install up to 1920 fibers per rack (7 foot tall, 23 inch wide, 12-fiber modules)
- > Available in black or gray.

Applications


- Backbone termination in telecommunications rooms or main distribution rooms
- ➤ Telco, Co-location, Point of Presence (POP), CLEC&CATV fiber deployement
- > Fiber interconnect cabinet
- > Cross-connect or interconnect configuration.

Technical specifications

Physical characteristics

Material


- > Steel, 16 gauge, powder paint finish
- > Smoked plexiglass door.



Packaging



AX100935 FiberExpress Manager Shelf



DIMENSION (n.)	w	н	01	D2
19 in.	19	7 (40)	11.8125	16
23 in.	23	7 (4U)	11.8125	16

MENTION, GABLE MANAGEMENT CHANNEL EQUIPMED OF BOOK

Alloy T (Alloy T)	UNIOADRO	LOADED
19 in.	10/3.2	25/11.5
23 in.	24/10.9	33.5/15.2

FiberExpress Manager Shelf (Tracé)



DATASheet

Packaging

- > The shelf (19 in. or 23 in.) comes with a hardware kit which includes the following:
 - 1 blank sheet (3 labels) for rack/shelf connection identification (Printing template can be found on our web site)
 - 1 pre-printed sheet (3 labels) for rack/shelf connection identification
 - 1 blank sheet (24 labels) for module identification (Printing template can be found on our web site)
 - 1 rack/shelf identification label

- 2 cable ties
- 3 Optical network saddles
- 8 Velcro straps, 20 cm (8 in.) long
- 2 Caution labels
- An installation guide (also available on our web site)
- ➤ The 19 in. version comes with 4 Pan Head Slotted/Phillips screws size 12-24
- ➤ The 23 in. version comes with 4 Pan Head Slotted/Phillips screws size 10-32.

For More Information

For any other product information call: 1 800 262-9334 • (514) 822-7533 or visit us at www.Beldenibdn.com

All information is subject to change without notice, since Belden CDT reserves the right to change its products as progress in engineering and manufacturing methods or other circumstances may warrant.

Ordering information

FiberExpress Manager Shelf

COLOR	WEIGHT	LENGTH	UPC	ORDERING NUMBER
GRAY	10.9 Kg (24 lb)	23 in.	628575059249	AX100934
BLACK	10.9 Kg (24 lb)	23 in.	628575059256	AX100935
GRAY	8.2 Kg (18 lb)	19 in.	628575060665	AX101084
BLACK	8.2 Kg (18 lb)	19 in.	628575060672	AX101085

