Zone 2

KEHFE/EXN, LKEHFV/EXN EXPLOSION-SAFE

C 🕻 🐼 II 3 GD; Ex nA II T4; Ex tD A22 IP65 T85°C 94/9/EC (ATEX) and 2004/108/EC (EMC) EN60079-15, EN60079-0, EN61241-1, EN61241-0

105dB(A)

MP3 Field Programmable Announciator, Melody Horn

- · Explosion-safe for gas and dust
- Suitable for Zone 2 and Zone 22
- CE compliance in accordance to ATEX
- · Super bright LED colors correspond to different voice, sounds, chimes and melodies.
- · Voice alert messages of up to 63 seconds (64kbit/s) with 5 channels can be played back.
- 32 combinations of sounds, chimes and melodies are pre-recorded.
- 8 sounds can be played back by a bit input, and 32 sounds by binary input.
- Volume is adjustable from 0 to 105dB at 1 meter.
- Field programmable with MP3 by SD card for the model LKEHFV/EXN.
- Well visible with the super bright 100mm diameter LED from far distance.

※ Height 1 Light: 265.2 2 Lights: 325.3 3 Lights: 385.4 4 Lights: 445.5

Mounting Dimension

Front

LED stack

3

3

3

З

2-ø10

(mm)

Power

14.2W

14 2W

14 2W

14.2W

- · Robust design to withstand against 2G vibration.
- The body is made of Acrylonitrite-Ethlene-Styrene for weather resistant.
- · Easy to control by only one common wire for both LED units and audible signals.
- NPN is standard. PNP open colletor type is also available on order.
- Protection rating of IP65

Dimensions

8

Shaft

A150

MP3

Supports

Supports

152

ø100

142

Model


LKEHFE-F/EXN

LKEHFE-W/EXN

I KEHEV-E/EXN

LKEHFV-W/EXN

%Height




 (ϵ)

RoHS


Sound Selection Charts

- 32 sounds are pre-recorded in one unit. 4 sound types are available.
- 8 sounds can be played back by a bit input, and 32 sounds by binary input.

Веер	Stutter + Bell	Inverted Revelle	Annie Laurie		
Stutter	Synthesized Melody	Galactic Motor	London Bridge		
Bell	Chime	Ringing Phone	Mary`s Lamb		
Yelp	Call Sign	Two Tone	Camptown Races		
Rapid Hi Lo	Train Ride	Alarm Clock	Amaryllis		
Melody Chime	Galloping Hi Lo	Ringing Hi Lo	Symphony #40		
Synthesized Piano	ynthesized Piano Alien Chatter		Ave Maria		
Synthesized Bell	Falling Crystals	Minuet	Grandfather's Clock		



Flush mount bracket for LKEHFE-F/EXN & LKEHFV-F/EXN



142

· LED units can be stacked to 1, 2, and 4 on order. · SD card for the model LKEHFV-F/EXN and

LKEHFV-W/EXN sold separately.

Specifications

-									
Model	Rated Voltage	Voltage Range	MP3, Melody	Operating Temperature	Recordable Duration	Sound Pressure (at 1m)	Mounting Brackets	Messages	Mass
LKEHFE-F/EXN		24VDC +/-10%	Type-E	-10C to +50C, Humidity 85% or less	Prerecorded	- 105dB	Flush mount	8ch bit input, 32ch binary input	2.8Kg
LKEHFE-W/EXN	24VDC		Type-E		Prerecorded		Wall mount	8ch bit input, 32ch binary input	3.2Kg
LKEHFV-F/EXN	24000		MPEG1-Audio layer III, 64kbit/s		63 sec.		Flush mount	5ch bit input, 31ch binary input	2.8Kg
LKEHFV-W/EXN			MPEG1-Audio layer III, 64kbit/s		63 sec.		Wall mount	5ch bit input, 31ch binary input	3.2Kg