

Product Catalog for CHIM Partner Support > Automotive Products > Automotive Electrical Products >

3M[™] Scissors Style TH-440



High carbon, heat-treated steel crimping tool that has a unique design that provides a high strength/weight ratio that crimps a broad range of 22-10 AWG terminals and connectors.

GTIN(UPC/EAN) : 0 00 54007 60825 7 3M Id : 80-6100-6484-4

3M[™] Scissors Style TH-440 Packaging

3M Id:	80-6100-6484-4
Minimum Order Quantity:	1.0 PACK
Case Quantity:	1.0 PACK

	English	Metric
Length	10.6 INCH	0.269 MTR
Width	5.5 INCH	0.140 MTR
Height	5.2 INCH	0.132 MTR
Gross Weight	5.1100 LBS	2.3179 KG

TH-440 Scissors Style

Acompact, high-quality tool designed to perform the six most common electrical wiring functions.

- Made of 1.125" (28,57 mm) heat-treated carbon steel
- Handles a variety of terminal and connector styles, insulated and non-insulated
- Range of 22–10 AWG
- 3M Terminals and Connectors are ULListed and CSACertified when used with the TH-440

Features:

- 1. Anvil-type wire cutter for clean cuts.
- 2. Crimp dies for 22-10 AWG insulated terminals, connectors and closed-end connectors.
- 3. Cut-off dies for mild steel and non-ferrous screws.
- 4. Crimp dies for 22–10 AWG non-insulated terminals and connectors.
- 5. Wire stripping stations for circumferencial cut-less effort.
- 6. Crimp die for 7 and 8 mm ignition parts.
- 7. Cushioned, vinyl grips, red.

For specific tooling applications, refer to the smallest unit container or the Tool Selection Guides in the Appendix.

Case

