



EPX™ Applicators and Nozzles

Technical Bulletin

July, 2010

Cartridge Size	35ml (10:1)	37ml (2:1)	50ml (1:1)	200ml (1:1 and 2:1)	250ml (10:1)	400ml (1:1 and 2:1)	12 oz
3M™ EPX™ Applicators – manual		EPX Metal Applicator (62-9740-9935-0) 2:1 Plunger (62-9744-9930-3)	EPX Metal Applicator (62-9740-9935-0) (Use 2:1 format) (62-9744-9930-3)	EPX 200ml Manual Applicator (62-9136-9930-2) Plunger** (62-9136-9938-5)	None	None	EPX 12 oz Manual Dispenser (62-9600-9935-6)
	EPX Plus II Applicator (62-9170-9930-1) 10:1 Plunger* (62-9170-9910-3)	EPX Plus II Applicator (62-9170-9930-1) 2:1 Plunger** (62-9170-9921-0)	EPX Plus II Applicator (62-9170-9930-1) 1:1 Plunger** (62-9170-9911-1)				
	None	EPX 50ml Pneumatic Applicator*** (62-9781-9930-5)	EPX 50ml Pneumatic Applicator (62-9781-9930-5)	EPX 200ml Pneumatic Applicator (62-9140-9930-4)	EPX 200ml Pneumatic Applicator (62-9140-9930-4)	EPX 400ml Pneumatic Applicator (62-9145-9930-3)	EPX 12 oz Pneumatic Dispenser (62-9602-9935-2)
					10:1 Conversion Kit for EPX 200ml Pneumatic Applicator (62-9174-9932-9)		
3M™ EPX™ Nozzles	10:1 Mixing Nozzle for the EPX Plus Applicator (62-9164-9930-4)	EPX Mixing Nozzle for 50ml Applicator (62-9742-9935-6)	EPX Mixing Nozzle for 50ml Applicator (62-9742-9935-6)	EPX 6mm Nozzle for 200ml/400ml Applicators**** (62-9142-9930-0)	10:1 Mixing Nozzle for the EPX 250ml Applicator (62-9165-9930-1)	EPX 6mm Nozzle for 200ml/400ml Applicators**** (62-9142-9930-0)	12 oz Blunt End Mix Tip (62-9606-9935-3)
		EPX Mixing Nozzle - Square Gold (62-9171-9153-8)	EPX Mixing Nozzle - Square Gold (62-9171-9153-8)	EPX Mixing Nozzle - Square Gold (62-9176-9127-1)		EPX Mixing Nozzle - Square Gold (62-9176-9127-1)	12 oz Tapered End Mix Tip (62-9607-9935-1)

*Must be ordered separately - not included with EPX Plus II applicator.

**Included with the applicator.

***This set-up does take special modification done by 3M.

****This nozzle is recommended for all low viscosity products.

Technical Bulletin

EPX™ Applicators and Nozzles

Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M and EPX are trademarks of 3M Company.
Printed in U.S.A.
©3M 2010 (7/10)