

# Have a Question? Chat with a Product Information Specialist

What can we help you find?


Email

**Buy Product** 

**Products Industries** Resources **About TE My Account Innovation Support Center** 

Request Sample

# 5646442-1 Product Details



#### 5646442-1

TE Internal Number: 5646442-1



🔁 View 3D PDF

#### 2mm Hard Metric PCB Mount Connectors (Z-PACK 2mm HM)

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Connector
- Connector Assembly
- Connector Style = Receptacle
- Type = Type D, 25 Column Interface Type = 2mm HM
  - View all Features

Add to My Part List

# **Quick Links**

Share

- Pricing & Availability Search for Tooling
- View Mating Products (2)
- Product Feature SelectorContact Us About This Product

Print

**Documentation & Additional Information** 

R/A RECEPTACLE ASSY, 176 POSN, TTR 8 ROW, TYPE D, Z-... (PDF, English)

#### Catalog Pages/Data Sheets:

None Available

#### **Product Specifications:**

• Connector, Z-PACK, 8 Row, 2mm HM (PDF, English)

#### **Application Specifications:**

Z-PACK 2mm HM Interconnection System for Board-to-Bo... (PDF, English)

#### **Instruction Sheets:**

· None Available

# CAD Files: (CAD Format & Compression Information)2D Drawing (DXF, Version O)

- 3D Model (IGES, Version O)
- 3D Model (STEP, Version O)

#### Additional Information:

Product Line Information

Find Similar Products

#### **Related Products:**

- Tooling
- Mating Products (2)

List all Documents

# Product Features (Please use the Product Drawing for all design activity)

#### **Product Type Features:**

- Product Type = Connector
- Connector Type = Connector Assembly
- PCB Mounting Orientation = Right Angle

### **Mechanical Attachment:**

- Board Mount = Free Board
- AMP Standard Option Number = 1

#### **Termination Features:**

- Interface Type = 2mm HM
- Termination End Plating = Tin over Nickel

#### Dimensions:

• Module Length (mm [in]) = 48.00 [1.891]

# **Body Features:**

Type = Type D, 25 Column

# **Contact Features:**

- Contact Configuration = ACTION PIN Post, Signal
- Feedthrough Post Length (mm [in]) = 3.30 [0.130]
- CompactPCI = Yes
- Contact Plating, Mating Area, Material = Performance-Based
- Grounding Contact = Without
- Contact Base Material = Phosphor Bronze

#### **Housing Features:**

- Connector Style = Receptacle
- Mating Alignment = With
- Mating Alignment Type = Multi-Purpose Center
- Housing Color = Gray
- Housing Material = Polyester GF
- UL Flammability Rating = UL 94V-0

#### **Configuration Features:**

- Number of Rows = 8
- Number of Positions = 176
- Crosstalk Version = Standard
- Shielded = No
- Rows Loaded = F, E, D, C, B, A, H, G

#### Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free
- RoHS/ELV Compliance History = Always was RoHS compliant

## Other:

• Brand = TE Connectivity

