


## Stylus® Alkaline Battery-Powered Pen Light







FL1 STANDARD	GREEN LED
31/2	<b>7</b> LUMENS
(1)	24h
	15 m
	59 cd



Case Material: machined aluminum case with anodized finish and non-slip, knurled grip. Available in black, gold or silver, red, blue, US Flag

Dimensions/Weight: Length: 6.21"; 15.17 cm Diameter: 0.375"; 0.95 cm 1.1 oz; 31.19 grams\*

Light Source: High intensity 5mm LED, impervious to shock with a 100,000 hour lifetime

Available in White, Blue (470nm), Red (624nm), Green (527nm), UV (365nm) or IR (880nm)

On/Off: Features a momentary blink switch and constant "on"

Battery: 3 "AAAA" size alkaline batteries.

Features: High intensity LED

Individually serialized for positive identification IPX4 Rated for water resistant operation. 2 meter impact resistance tested Removable pocket clip.

Glare guard protector included in package

Approvals\*\*: UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C "Classified" (applies to specific model)

C-UL UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C; "Exia" (applies to specidic model)

ATEX: II 1G EEx ia IIC T1; DEMKO 04 ATEX 0410949 (applies only to Black case/White or Blue LED combinations)

Most models meet applicable European Community Directives.

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work as a result of a manufacturing defect for as long as you own it. This limited lifetime

warranty excludes abuse, battery leakage and normal wear and tear.

<sup>\*\*</sup>See product for specific ratings.

Item		UPC	Part #	
English packaging				
Stylus	Black with Red LED	080926-65006-0	65006	
Stylus	Black with Blue LED	080926-65022-0	65022	
Stylus	Black with Green LED	080926-65020-6	65020	
Stylus	Black with White LED	080926-65018-3	65018	
Stylus UL Listed	Black with White LED	080926-65058-9	65058	
Stylus	Black with UV LED	080926-65069-5	65069	
Stylus	OD with IR LED	080926-65186-9	65183	
Stylus	US Flag with White LED	080926-65080-0	65080	
See reverse for additional part numbers				



<sup>\*</sup>With battery (included in purchase).





Item	UPC	Part #
Multilingual packaging	•	
Stylus Black. Blister packaged - White LED	080926-68115-0	65118
Stylus Black. Blister packaged - Blue LED	080926-65022-0	65022
Stylus - Black Blister packaged - Red LED	080926-65106-7	65106
Stylus - Black Blister packaged - Blue LED (ATEX)	080926-65083-3	65083
Stylus - Black Blister packaged - Green LED	080926-65120-3	65120
Stylus - Black Blister packaged - White LED (ATEX)	080926-65082-4	65082
Stylus - UL Listed Black White LED	080926-65058-9	65058
Stylus - Gold Blister packaged - White LED	080926-65124-1	65124
Stylus - Silver - Blister packaged - Blue LED	080926-65116-6	65116
Stylus - Silver - Blister packaged - White LED	080926-65112-8	65112
Stylus - Blue - Blister packaged - White LED	080926-65150-0	65150
Stylus - Red - Blister packaged - White LED	080926-65135-7	65135
Stylus - Black - Blister packaged -UV LED	080926-65070-1	65070
Stylus - US Flag - Blister packaged -White LED	080926-65180-7	65180
Lanyard with Push Button Slide (not shown)	080926-72024-4	72024
AAAA Batteries – 6 pack	080926-65030-5	65030

